


E18164



Female wirable connectors

SDOGH040VASFKPG7



Application

Application Industrial applications

Electrical data

Operating voltage [V] < 250 AC / < 300 DC
Max. current load total [A] 4

Operating conditions

Ambient temperature [°C] -40...85
Protection IP 68

Mechanical data

Weight [g] 45.359
Dimensions [mm] 18 x 18 x 46
Molded-body material PA
Material nut stainless steel (1.4571/316Ti)

Remarks

Pack quantity 1 pcs.

Electrical connection

terminals: ...0.75 mm²; Cable sheath: Ø 4...6 mm

Electrical connection - Socket

Connector: 1 x M12, straight; coding: A; Contacts: 4, pre-coppered brass; Moulded body: PA; Locking: stainless steel (1.4571/316Ti)



Connection

