


E12582



Wirable AMP socket

SDOGV060--AFKCR



Application		
Application		Use in mobile and harsh applications
Electrical data		
Operating voltage	[V]	12...24 DC
Operating conditions		
Ambient temperature	[°C]	-40...100
Ambient temperature (moving)	[°C]	-40...100
Protection		IP 67; (mating connector plugged in)
Mechanical data		
Weight	[g]	14
Dimensions	[mm]	29.8 x 26.4 x 31.5
Material		socket housing: PBT; Contacts: tin-plated
Accessories		
Items supplied		cover plug: 6
		sealing of the individual cores: 2 x 0,5 mm²
		sealing of the individual cores: 4 x 2,5 mm²
		Crimp contacts: 6
Remarks		
Pack quantity		1 pcs.
Electrical connection		
terminals: 2 x 0.5 mm²		
4 x 2.5 mm²		
Electrical connection - Socket		
Connection		
Connector: 1 x AMP connector, straight; Contacts: tin-plated		