

Programmable controller for mobile machines


R360/32 bit Ext/EIOS/80 I/O

Article to be discontinued

Alternative articles: CR721S

When selecting an alternative article and accessories please note that technical data may differ!

Please do not use for new projects.


Electrical data

Operating voltage	[V]	8...32 DC
-------------------	-----	-----------

Inputs / outputs

Total number of inputs and outputs	80
Number of inputs and outputs	Number of digital inputs: 40; Number of analog inputs: 36; Number of frequency inputs: 36; Number of resistor inputs: 4; Number of digital outputs: 40; Number of outputs with H-bridge: 4

Inputs

Number of frequency inputs	36	
Number of resistor inputs	4	
Number of digital inputs	40	
Number of analog inputs	36	
Analog input (current)	[mA]	0...20
Analog input (voltage)	[V]	0...32

Outputs

Number of digital outputs	40
Number of PWM outputs	32
Number of PWM-I outputs	32
Number of outputs with H-bridge	4

Software / programming

Parameter setting options	input/output functions
PLC function to IEC 61131-3	yes

CR0235



Programmable controller for mobile machines

R360/32 bit Ext/EIOS/80 I/O

Interfaces		
Number of CAN interfaces		4
Number of R232 interfaces		1
Number of USB interfaces		1
Tests / approvals		
MTTF	[years]	21
Mechanical data		
Weight	[g]	136.5
Housing		rectangular
Type of mounting		screw mounting
Dimensions	[mm]	153 x 277 x 43
Remarks		
Notes		Please do not use for new projects.
Pack quantity		1 pcs.