


E40240



Mounting adapter for flow sensors

ADAPT G2 FLANGE ADJUSTABLE



ACS

Application		
Design	for flow sensors Typ SM2, SM9	
Installation	SM2 SM9	
Pressure rating	16 bar	1.6 MPa
Mechanical data		
Weight	[g]	2255.5
Type of mounting	Adapter; (rotatable)	
Materials	flange: stainless steel (304/1.4301); Adapter: stainless steel (316Ti/1.4571); O-ring: EPDM 47,22 x 3,53 mm	
Sensor connection	G 2	

E40240



Mounting adapter for flow sensors

ADAPT G2 FLANGE ADJUSTABLE

Process connection	flange DN50 according to DIN2642 / EN1092-1 type 2
Accessories	
Items supplied	O-rings: 2
Remarks	
Pack quantity	2 pcs.