



# AS-i modules for hygienic areas

Field modules with ecolink M12 screw connection

- The special plastic housing meets the high requirements for food production
- The ecolink screw connection offers ingress resistance up to IP69K
- Robust thanks to full potting
- Wide operating temperature range and high protection rating
- Clearly visible LEDs for operation, switching status and fault indication



**ifm** – close to you!

Version	Current rating per port	Connection technology	Order no.
Passive splitter box, 4 ports	4 A	AS-i / IO-Link	<b>AC2950</b>
Passive splitter box, 8 ports	4 A	AS-i / IO-Link	<b>AC2951</b>
I/O module 2x (2 DI / 1 DO), 2 ports	100 mA (output, supply via AS-i)	AS-i	<b>AC2952</b>
I/O module 4x DI-Y, 4 ports	–	AS-i	<b>AC2954</b>

**Robust for demanding applications**

The special PA housing design, the stainless steel connectors and the high ingress resistance to IP69K enable permanent use in areas with frequent intensive cleaning processes, for example in the food and beverage industry. Thanks to full potting, both the modules themselves and the ecolink M12 connectors reliably withstand shock and vibration loads over the long term. By the way: the ecolink connections are compatible with the M12 connectors usual in industry. However, maximum ingress resistance is only ensured with the ifm ecolink connectors.

**Versions**

**Passive splitter boxes**

Passive voltage splitters essentially function like “multiple sockets” for AS-i networks, but also for IO-Link structures. They enable the voltage supply of components such as valve heads, quarter-turn sensors, motor controls and IO-Link masters. Short circuits and excessively high currents are clearly signalled by a red LED. This helps to quickly recognise and rectify malfunctions or damage to the infrastructure, the actuators or the entire system.

Common technical data		
Ambient temperature	[°C]	-25...60
<b>Materials</b> Housing Connector Sealing		PA grey Stainless steel (316L / 1.4404) EPDM
Protection rating		IP65, IP66, IP67, IP69K (operation with stainless steel protective caps: IP69K)

**I/O modules**

Digital I/O modules enable the connection of sensors and actuators that communicate with the controller via the AS-Interface. In contrast to conventional AS-i modules, the modules here do not use flat cable insulation displacement technology, but M12 round cable connection technology - both at the I/O ports and at the AS-i connection. In this way, they fulfil the special requirements for wet areas.

**BEST FRIENDS**

We reserve the right to make technical alterations without prior notice. · 11.2024  
ifm electronic gmbh · Friedrichstr. 1 · 45128 Essen



**AS-i gateway**  
With PROFINET interface and integrated PLC



**Inductive sensors**  
Robust stainless steel housing for the food industry



**AS-i illuminated pushbutton module**  
Illuminated buttons in stainless steel housing



For further technical details, please visit:  
[ifm.com/fs/AC2950](http://ifm.com/fs/AC2950)