



More efficiency in every way

Fast-response, precise flow sensor

- Reliable process quality through continuous monitoring of the conformal temperature control
- Contributes to precise process control and reduced material waste
- Modern energy management combined with temperature sensors
- Capable of withstanding temperatures up to 180 °C and pressures up to 30 bar



IP67

ifm – close to you!

Measuring range [l/min]	Process connection	Order no.
0.3...25	Rp 3/4	SBT633
0.6...50	Rp 3/4	SBT634
2...100	Rp 1	SBT646
4...200	Rp 1 1/2	SBT657

Efficient production ensuring the required level of quality

The SBT type flow sensors ensure quality and efficiency in your production processes, for example in injection moulding plants, tyre production or meat substitute production. The sensor quickly and precisely determines the flow rate of the medium used for the conformal temperature control in order to heat or cool the mould depending on the process step. In the process, it will not be affected by air bubbles.

Thanks to the high repeatability, deviations from the setpoint are detected at an early stage, even when the flow rates are very low. Costly material waste due to premature or incomplete cooling is avoided.


Early identification of maintenance requirements

Depending on the nature of the heating or cooling medium, the channels incorporated into the injection mould for conformal temperature control can become clogged over time. Deposits such as lime or dirt particles can reduce or even prevent the flow of the heating or cooling medium. The precise sensor technology helps to quickly identify the maintenance requirements in the clogged piping system and to prevent quality degradation.

Common technical data		
Medium temperature	[°C]	10...180
Accuracy	[%]	± 5
Response time	[s]	< 0.01
Protection rating		IP67

Modern energy management


Monitoring the flow and temperature has proven its worth in temperature control processes. In this way, the energy consumption of the production process can be easily monitored and optimised through precise control of temperature and flow.



- 1) Temperature control unit
- 2) Tool

BEST FRIENDS


We reserve the right to make technical alterations without prior notice. · 04.2023
ifm electronic gmbh · Friedrichstr. 1 · 45128 Essen



Temperature transmitters
Precise and fast detection of temperatures up to 200 °C



IO-Link converter
For connecting analogue sensors, with display



Temperature sensor
Precise and fast detection of temperatures up to 150 °C



For further technical details, please visit:
ifm.com/fs/SBT633