



Fast, precise, non-invasive

Passive surface temperature probe

- Clamp-on solution reduces installation costs and effort
- Also suitable for use in hygienic areas
- Fast response time and high measurement accuracy for a clear process overview



IP69K

ifm – close to you!

External pipe diameter [mm]	Nominal width	Order no.
21...24	DN20	TSM301
25...30	DN25	TSM401
32...36	DN32	TSM501
38...45	DN40	TSM601
48...54	DN50	TSM701

Common technical data		
Temperature measuring range	[°C]	-25...160
Measurement accuracy	[%]	2
Measuring element		Pt1000
Response time T09	[s]	25
Protection rating		IP69K

Simple process monitoring even on small pipes

The temperature probe for surface mounting enables quick, flexible and easy measuring point configuration. The passive temperature probe is particularly suitable for use on small pipe diameters where invasive temperature monitoring would significantly affect the flow of the medium. As the values are recorded non-invasively, there is no risk of contamination of the medium. Instead, the installation is easy and does not require time-consuming and cost-intensive drilling and welding, so that the measuring point can also be installed in the running process.

Tested hygienic suitability

Thanks to a temperature range of up to 160 °C, high protection rating IP69K and the hygienically safe mounting principle tested by Ecolab, the probe is also suitable for use in food production. In combination with invasive temperature monitoring, for example, complete heating of the pipes required in the CIP process can be ensured.

BEST FRIENDS

We reserve the right to make technical alterations without prior notice. · 04.2024
ifm electronic gmbh · Friedrichstr. 1 · 45128 Essen



Temperature plug
Converts resistance values into analogue or IO-Link signals



moneo|blue
Manage IO-Link devices conveniently via smartphone app



IO-Link masters
Field-compatible masters for use in hygienic areas



For further technical details, please visit:
ifm.com/fs/TSM301