
SM2001

Magnetic-inductive flow meter

SMR21XGXFRKG/US



CE CRN cULus LISTED EC 1935/2004 FCM JP IO-Link UKCA

Product characteristics		
Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1	
Measuring range	80...9600 gph	1.3...160 gpm
Process connection	threaded connection G 2 external thread DN50 flat seal	

Application	
Special feature	Gold-plated contacts
Application	totaliser function; empty pipe detection; for industrial applications
Installation	connection to pipe by means of an adapter
Media	conductive liquids; water; hydrous media

SM2001

Magnetic-inductive flow meter

SMR21XGXFRKG/US

Note on media		conductivity: ≥ 20 µS/cm		
		viscosity: < 70 mm²/s (40 °C)		
Medium temperature	[°F]	14...194		
Pressure rating		16 bar	232 psi	1.6 MPa
MAWP for applications according to CRN		8.9 bar	0.89 MPa	
Electrical data				
Operating voltage	[V]	18...32 DC; (to SELV/PELV)		
Current consumption	[mA]	< 150		
Min. insulation resistance	[MΩ]	100; (500 V DC)		
Protection class		III		
Reverse polarity protection		yes		
Power-on delay time	[s]	5		
Measuring principle		magnetic-inductive		
Inputs / outputs				
Number of inputs and outputs		Number of digital outputs: 2; Number of analogue outputs: 1		
Inputs				
Inputs		counter reset		
Outputs				
Total number of outputs		2		
Output signal		switching signal; analogue signal; pulse signal; frequency signal; IO-Link; (configurable)		
Electrical design		PNP/NPN		
Number of digital outputs		2		
Output function		normally open / normally closed; (parameterisable)		
Max. voltage drop switching output DC	[V]	2		
Permanent current rating of switching output DC	[mA]	250; (per output)		
Number of analogue outputs		1		
Analogue current output	[mA]	4...20; (scalable)		
Max. load	[Ω]	500		
Analogue voltage output	[V]	0...10; (scalable)		
Min. load resistance	[Ω]	2000		
Pulse output		flow rate meter		
Short-circuit protection		yes		
Type of short-circuit protection		pulsed		
Overload protection		yes		
Frequency of the output	[Hz]	0.1...10000		
Measuring/setting range				
Measuring range		80...9600 gph	1.3...160 gpm	
Display range		-11520...11520 gph	-190...190 gpm	
Resolution		5 gph	0.1 gpm	
Set point SP		130...9600 gph	2.1...160 gpm	
Reset point rP		80...9550 gph	1.3...159.2 gpm	
Analogue start point ASP		0...7680 gph	0...128 gpm	

SM2001

Magnetic-inductive flow meter

SMR21XGXFRKG/US

Analogue end point AEP		1920...9600 gph	32...160 gpm
Low flow cut-off LFC		< 240 gph	< 4 gpm
In steps of		5 gph	0.1 gpm
Measuring dynamics		1:120	
Volumetric flow quantity monitoring			
Pulse value		0.02...160 E06 gal	
In steps of		0.02 gal	
Pulse length	[s]	0,008...2	
Temperature monitoring			
Measuring range	[°F]	-4...176	
Display range	[°F]	-40...212	
Resolution	[°F]	0.5	
Set point SP	[°F]	-2...176	
Reset point rP	[°F]	-3...175	
Analogue start point	[°F]	-4...140	
Analogue end point	[°F]	32...176	
In steps of	[°F]	0.5	
Accuracy / deviations			
Flow monitoring			
Accuracy (in the measuring range)		± (0,8 % MW + 0,5 % MEW)	
Repeatability		± 0,2% MEW	
Temperature monitoring			
Temperature drift		± 0,0185 °F / K	
Accuracy	[K]	± 1 (77 °F; Q > 4 gpm)	
Response times			
Flow monitoring			
Response time	[s]	0.35; (dAP = 0)	
Delay time programmable dS, dr	[s]	0...50	
Damping process value dAP	[s]	0...5	
Temperature monitoring			
Dynamic response T05 / T09	[s]	T09 = 3 (Q > 4 gpm)	
Software / programming			
Parameter setting options		Flow monitoring; quantity meter; Preset counter; Temperature monitoring; hysteresis / window; normally open / normally closed; switching logic; current/voltage/frequency/ pulse output; start-up delay; display can be deactivated; Display unit; empty pipe detection	
Interfaces			
Communication interface		IO-Link	
Transmission type		COM2 (38,4 kBaud)	
IO-Link revision		1.1	
SDCI standard		IEC 61131-9 CDV	

SM2001

Magnetic-inductive flow meter

SMR21XGXFRKG/US

Profiles		Smart Sensor - SSP 0	Generic Profiled Sensor
		Function	Device identification
		Function	Process data variable
SIO mode		yes	
Required master port type		A	
Process data analogue		3	
Process data binary		2	
Min. process cycle time	[ms]	5	
Supported DeviceIDs		**Type of operation**	**DeviceID**
		default	390

Operating conditions		
Ambient temperature	[°F]	14...140
Storage temperature	[°F]	-13...176
Protection		IP 65; IP 67

Tests / approvals			
EMC		DIN EN 60947-5-9	
Shock resistance		DIN EN 60068-2-27	20 g (11 ms)
Vibration resistance		DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF	[years]	85	
UL approval		UL approval no.	I008
		File number UL	E174189
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	

Mechanical data		
Weight	[g]	3069.2
Housing		rectangular
Inlet pipe length		3 x DN
Outlet pipe length		1 x DN
Dimensions	[mm]	200 x 103 x 117
Materials		stainless steel (316L/1.4404); stainless steel (316Ti/1.4571); PEI; FKM; PBT-GF20; TPE-U
Materials (wetted parts)		Pipe section: stainless steel (316L/1.4404); Process connection sealing: NBR reinforced fibre Flat seal; FKM; stainless steel (316Ti/1.4571); PEEK
Process connection		threaded connection G 2 external thread DN50 flat seal

Displays / operating elements		
Display	Display unit	6 x LED, green (gpm, gph, gal, °F, 10^3, 1000 x 10^3)
	switching status	2 x LED, yellow
	measured values	alphanumeric display, 4-digit
	programming	alphanumeric display, 4-digit

Accessories	
Items supplied	sealings: 2, Centellen
	Label

Remarks	
Remarks	MW = measured value
	MEW = Final value of the measuring range
Pack quantity	1 pcs.

SM2001

Magnetic-inductive flow meter


SMR21XGXFRKG/US

Electrical connection

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



Connection



	colours to DIN EN 60947-5-2
OUT1:	switching output empty pipe detection
	switching output volumetric flow quantity monitoring
	frequency output volumetric flow quantity monitoring
	Pulse output quantity meter
	signal output Preset counter
	IO-Link
OUT2:	switching output empty pipe detection
	switching output volumetric flow quantity monitoring
	switching output Temperature monitoring
	analogue output volumetric flow quantity monitoring
	analogue output Temperature monitoring
	input counter reset
	Core colours :
BK =	black
BN =	brown
BU =	blue
WH =	white


SM2001

Magnetic-inductive flow meter

SMR21XGXFRKG/US

Diagrams and graphs

Pressure loss



dP Pressure loss

Q volumetric flow quantity