




Evaluation unit with display for PT100/PT1000 temperature sensors

TR-000KDBM12-MFPKG/US/



- 1 LEDs Display unit / switching status
- 2 alphanumeric display 4-digit red/green
- 3 programming buttons



Product characteristics

Number of inputs and outputs	Number of digital outputs: 1; Number of analogue outputs: 1	
Measuring range	-100...600 °C	-148...1112 °F
Communication interface	IO-Link	
Process connection	threaded connection G 1/2 external thread	

Application

Special feature	Gold-plated contacts
Application	for Pt100 and Pt1000 measuring elements

Electrical data

Operating voltage	[V]	18...32 DC; ("supply class 2" to cULus)
Current consumption	[mA]	< 50
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	1
Integrated watchdog		yes

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 1; Number of analogue outputs: 1
------------------------------	---

Outputs

Total number of outputs	2
Output signal	switching signal; analogue signal; IO-Link; (configurable)
Electrical design	PNP/NPN



Evaluation unit with display for PT100/PT1000 temperature sensors

TR-000KDBM12-MFPKG/US/

Number of digital outputs	1	
Output function	normally open / normally closed; (parameterisable)	
Max. voltage drop switching output DC [V]	2.5	
Permanent current rating of switching output DC [mA]	250	
Number of analogue outputs	1	
Analogue current output [mA]	4...20	
Max. load [Ω]	500	
Analogue voltage output [V]	0...10	
Min. load resistance [Ω]	2000	
Short-circuit protection	yes	
Type of short-circuit protection	pulsed	
Overload protection	yes	
Measuring/setting range		
Measuring range	-100...600 °C	-148...1112 °F
Factory setting	-40...300 °C / -40...572 °F	
Set point SP	-99.8...600 °C	-147.6...1112 °F
Reset point rP	-100...599.8 °C	-148...1111.6 °F
Analogue start point	-100...595 °C	-148...1103 °F
Analogue end point	-95...600 °C	-139...1112 °F
In steps of	0.1 °C	0.1 °F
Resolution		
Resolution of switching output [K]	0.1	
Resolution of analogue output [K]	current output: MS / 4096; voltage output: MS / 3561	
Resolution of display [K]	0.1	
Accuracy / deviations		
Switch point accuracy [K]	± 0,3 + (± 0,1 % MS)	
Precision analogue output [K]	± 0,3 + (± 0,1 % MS)	
Display accuracy [K]	± 0,3 + (± 0,1 % MS)	
Temperature coefficient [% of the span / 10 K]	0,1; (in case of deviation from the reference condition 25 ± 5 °C)	
Response times		
Response time [ms]	390	
Max. response time analogue output [ms]	390	
Software / programming		
Parameter setting options	hysteresis / window; normally open / normally closed; switch-on/switch-off delay; Damping; Display unit; current/voltage output	
Interfaces		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	



Evaluation unit with display for PT100/PT1000 temperature sensors

TR-000KDBM12-MFPKG/US/

Profiles	Smart Sensor - SSP 0		Generic Profiled Sensor
	Function		Device identification
	Function		Process data variable
	Function		Device diagnosis
Min. process cycle time	[ms]	2.3	
Supported DeviceIDs	Type of operation	DeviceID	
	default	584	

Operating conditions			
Ambient temperature	[°C]	-25...80	
Storage temperature	[°C]	-40...100	
Protection		IP 67	

Tests / approvals			
EMC	DIN EN 61000-6-3		
	DIN EN 61000-6-2		
Shock resistance	DIN IEC 68-2-27	50 g (11 ms)	
Vibration resistance	DIN EN 60068-2-6	20 g (10...2000 Hz)	
MTTF	[years]	233	

Mechanical data			
Weight	[g]	200	
Housing		cylindrical	
Dimensions	[mm]	Ø 34 / L = 104	
Materials		Process connection: stainless steel (303/1.4305); housing: stainless steel (316L/1.4404); PBT+PC-GF30; PC; Connection: PEI; TPU; O-ring: FKM	
Process connection		threaded connection G 1/2 external thread	

Displays / operating elements			
Display	Display unit	2 x LED, green	
	switching status	LED, yellow	
	measured values	alphanumeric display, red/green 4-digit	

Remarks			
Remarks	MS = set measuring span		
Pack quantity	1 pcs.		

Electrical connection			
Connector: 1 x M12; coding: A; Contacts: 4, gold-plated			



Evaluation unit with display for PT100/PT1000 temperature sensors

TR-000KDBM12-MFPKG/US/

Connection



OUT1: switching output / IO-Link
OUT2: analogue output
colours to DIN EN 60947-5-2