
E20825

Fibre optic through-beam sensor

FE-50-V-V-M5/16/R



Application		
Function principle		Through-beam sensor
Detection zone		
Range with fibre-optic amplifier type		OBF; ODF; OMF
OBF		
Range of fibre optics	[mm]	1000
ODF		
Range of fibre optics	[mm]	4
OMF		
Range of fibre optics	[mm]	800
Operating conditions		
Ambient temperature	[°C]	-58...315
Mechanical data		
Weight	[g]	204
Version of sensing head		angled
Sensing head thread		5/16 x 24
Sensing head length	[mm]	58
Total length	[mm]	900
Min. bending radius	[mm]	19

E20825

Fibre optic through-beam sensor

FE-50-V-V-M5/16/R

Fibre arrangement	◉
Fibre material	glass
Fibre head material	stainless steel (303/1.4305)
Fibre sheath material	stainless steel (303/1.4305)
Accessories	
Items supplied	hexagon nuts: 4 x M8
	clamping rings: 2
	O-rings: 2
Remarks	
Pack quantity	1 pcs.