
DI5033

Compact evaluation unit for speed monitoring

DMC3020BWRKG/IO/US



1 LED yellow
2 LED green

Product characteristics		
Electrical design		PNP/NPN
Output function		normally open / normally closed; (parameterisable)
Sensing range	[mm]	20
Communication interface		IO-Link
Housing		rectangular
Dimensions	[mm]	40 x 40 x 54
Application		
Application		simple evaluation of rotating and linear movement with regard to underspeed; blocking
Electrical data		
Nominal voltage DC	[V]	10...30
Current consumption	[mA]	< 10
Protection class		III
Reverse polarity protection		yes
Outputs		
Electrical design		PNP/NPN
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100

DI5033

Compact evaluation unit for speed monitoring

DMC3020BWRKG/IO/US

Short-circuit proof		yes	
Overload protection		yes	
Detection zone			
Sensing range	[mm]	20	
Sensing range adjustable		no	
Operating distance	[mm]	0...16.2	
Measuring/setting range			
Setting range	[Imp/min]	5...9600	
Measuring principle		inductive	
Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3	
Hysteresis	[% of Sr]	10	
Response times			
Start-up delay	[s]	0...30; (In steps of: 100 ms; Default: 15 s)	
Max. damping frequency	[Imp/min]	12000	
Interfaces			
Communication interface		IO-Link	
Transmission type		COM2 (38,4 kBaud)	
Profiles		Smart Sensor - SSP 0	Generic Profiled Sensor
		Function	Device identification
		Function	Multiple switching signal
		Function	Process data variable
		Function	Device diagnosis
		Function	Teach channel
Min. process cycle time	[ms]	3.2	
Supported DeviceIDs		**Type of operation**	**DeviceID**
		default	913
Operating conditions			
Ambient temperature	[°C]	-25...80	
Storage temperature	[°C]	-25...80	
Protection		IP 67	
Tests / approvals			
EMC		EN 61000-4-2 ESD	4 kV CD / 8 kV AD
		EN 61000-4-3 HF radiated	10 V/m
		EN 61000-4-4 Burst	2 kV
		EN 61000-4-6 HF conducted	10 V
		EN 55011	class B
		EN 60947-5-2	
MTTF	[years]	639	
UL approval		UL approval no.	A009
Mechanical data			
Weight	[g]	175	
Housing		rectangular	
Mounting		flush mountable	

DI5033

Compact evaluation unit for speed monitoring

DMC3020BWRKG/IO/US

Dimensions	[mm]	40 x 40 x 54	
Materials		housing: PA	

Displays / operating elements

Display	operation	LED, green
	SIO mode	
	output stage supplied with current	4 x LED, yellow
	IO-Link mode	
	target in measuring range	4 x LED, yellow
	target outside measuring range	4 x LED, yellow flashing

Remarks


Pack quantity	1 pcs.


Electrical connection

Connector: 1 x M12; coding: A; Contacts: 4; Moulded body: brass, white bronze coated



Connection





4: OUT / IO-Link