


KTE101

Capacitive touch sensor

KTEEFOKMMFRKG/US/IO



Product characteristics	
Electrical design	PNP/NPN; (configurable)
Output function	normally open / closed; (configurable)
Communication interface	IO-Link
Housing	Threaded type
Dimensions [mm]	M22 x 1 / L = 39.7
Application	
Principle of operation	dynamic; static; Bistable; combination; (configurable)
UV resistant	yes
Electrical data	
Operating voltage [V]	8...32 DC
Protection class	III
Reverse polarity protection	yes
Current consumption	< 7,2 mA; (LED off: Ub = 24 V) < 125 mA; (LED white, max. brightness: Ub = 8 V) < 79 mA; (LED white, max. brightness: Ub = 12 V) < 43 mA; (LED white, max. brightness: Ub = 24 V) < 35 mA; (LED white, max. brightness : Ub = 32 V)
Inputs	
Total number of inputs	2
Switching level high [V]	> 19.2; (at 24 V safely on : Voltage >= Ub*0,8)
Switching level low [V]	< 4.8; (at 24V safely off : Voltage <= Ub*0,2)
Inputs	according to the standard IEC 61131-2 (Typ 3)
Outputs	
Electrical design	PNP/NPN; (configurable)
Output function	normally open / closed; (configurable)



Capacitive touch sensor

KTEEF0KMMFRKG/US/IO

Max. voltage drop switching output DC	[V]	1.5	
Permanent current rating of switching output DC	[mA]	200	
Short-circuit protection		yes	
Overload protection		yes	
Reaction times			
Response time	[ms]	64	
Software / programming			
Parameter setting options		normally open / closed; PNP/NPN; static; dynamic; Bistable; combination; Switch-on and switch-off delay; brightness; sensitivity; Operating conditions	
Interfaces			
Communication interface		IO-Link	
Transmission type		COM2 (38,4 kBaud)	
IO-Link revision		1.1.3	
Profiles		Smart Sensor - SSP 1.1	Fixed Switching Sensor
		Common - I&D	Identification and Diagnosis
		Extension	Sensor Control Wide
		Function	Locator
		Function	ProductURI
Min. process cycle time	[ms]	13.2	
Supported DeviceIDs		Type of operation	DeviceID
		default	1559
Operating conditions			
Ambient temperature	[°C]	-30...65	
Protection		IP 65; IP 67; (IP 69K on the front)	
Tests / approvals			
EMC		EN 61000-4-2 ESD	4 kV CD / 8 kV AD
		EN 61000-4-3 HF radiated	10 V/m / 3 V/m
		EN 61000-4-4 Burst	2 kV
		EN 61000-4-6 HF conducted	10 V
		IEC 61000-6-3, EN 55011	(Class B)
		IEC 61000-4-5 Surge	1 kV (L+ to L- , 42 Ω, 0,5 μF) / 0,5 kV (all cables to L- , 42 Ω, 0,5 μF)
Vibration resistance		EN 60068-2-6 Fc	20 g (10...3000 Hz) / 50 sweep cycles per frequency; 1 octave per minute in 3 axes
Shock resistance		EN 60068-2-27 Ea	50 g 11 ms half-sine; 20 shocks each in every direction of the 3 coordinate axes
Continuous shock resistance		EN 60068-2-29 Eb	40 g 6 ms half-sine; 8000 shocks each in every direction of the 3 coordinate axes
MTTF	[years]	218	
Mechanical data			
Weight	[g]	48.4	
Housing		Threaded type	
Dimensions	[mm]	M22 x 1 / L = 39.7	
Thread designation		M22 x 1	
Material		housing: PA; lock nut: PBT; Symbol disc: PA; Gasket: NR	

KTE101



Capacitive touch sensor

KTEEFOKMMFRKG/US/IO

Displays / operating elements

Display	Power	LED, RGB configurable
---------	-------	-----------------------

Accessories


Items supplied	lock nuts: 1 x M22
	transparent symbol disc: 1
	symbol sticker: 1
	Gasket: 1
	O-ring: 1
Accessories (optional)	Symbol disc

Remarks


Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A; Contacts: 5



Connection



1	L+	
2	IN1	
3	L-	
4	MP	DO (NO/NC), IO-Link
5	IN2	


MP: multifunctional input; DO: digital output; NO: normally open; NC: normally closed

Capacitive touch sensor

KTEEFOKMMFRKG/US/IO

Diagrams and graphs

application note relevant for the function



function
only
ensured
with
symbol
disc
(can
be
ordered
separately)

1. function ensured with plastic disc
2. function not ensured without disc
3. function ensured with stainless steel disc