
ANT411

RFID read/write head HF

DTRHF FNRWIDUS03



Application			
Application		detection of objects on transport equipment	
Radio approval for		USA; Canada; EU/RED; Australia; Japan; China; Taiwan; India; South Korea; Singapore; Ukraine	
Note on radio approval		The list of countries applying the European Radio Equipment Directive 2014/53/EU (RED) can be found under “Downloads”.	
Electrical data			
Operating voltage	[V]	19.2...28.8 DC; (supply only via the DTE10x evaluation unit (to EN 60950-1))	
Current consumption	[mA]	< 50	
Protection class		III	
Operating frequency	[MHz]	13,56	
RFID standard		ISO 15693	
Detection zone			
Distance write/read head front	[mm]	90	
Distance write/read head side	[mm]	25	
Distance to the ID tag	[mm]	referred to 20 mm coin tag; I-CODE SLI	: ≤ 18
		only for static applications	
Interfaces			
Communication interface		DATA / DTE10x	
Operating conditions			
Ambient temperature	[°C]	-20...60	
Storage temperature	[°C]	-25...80	
Protection		IP 67; IP 69K	
Tests / approvals			
Shock resistance		EN 60068-2-27	40 g 6 ms / repetitive
		EN 60068-2-27	50 g 11 ms / not repetitive
Vibration resistance		EN 60068-2-6	20 g 10...2000 Hz
MTTF	[years]	614	
Mechanical data			
Weight	[g]	83.75	
Housing		threaded type	
Mounting		non-flush mountable	

ANT411

RFID read/write head HF

DTRHF FNRWIDUS03

Dimensions [mm]	M12 x 1 / L = 70	
Thread designation	M12 x 1	
Materials	housing: stainless steel; Protective cover: PPS	
Displays / operating elements		
Display	operation	1 x LED, green
	tag communication	1 x LED, yellow
Accessories		
Items supplied	lock nuts: 2 x M12	
Remarks		
Remarks		
Pack quantity	1 pcs.	
Electrical connection		

Connector: 1 x M12; coding: A; Contacts: 4



Connection

