
KT5005

Capacitive touch sensor

KTRSHMK-RBPKG/AM/2M



Product characteristics		
Electrical design		PNP
Output function		normally open
Housing		cylindrical
Dimensions	[mm]	Ø 100 / L = 11
Application		
Operating principle		static
Electrical data		
Operating voltage	[V]	12...30 DC
Current consumption	[mA]	30

KT5005

Capacitive touch sensor

KTRSHMK-RBPKG/AM/2M

Protection class			III
Reverse polarity protection			yes
Max. power-on delay time	[ms]		500
Outputs			
Electrical design			PNP
Output function			normally open
Permanent current rating of switching output DC	[mA]		200
Short-circuit protection			yes
Overload protection			yes
Response times			
Response time	[ms]		35
Operating conditions			
Ambient temperature	[°C]		-40...85
Protection			IP 67; IP 69K; (on the front)
Tests / approvals			
MTTF	[years]		394
Mechanical data			
Weight	[g]		158.5
Housing			cylindrical
Dimensions	[mm]		Ø 100 / L = 11
Materials			active face: PA Grilamid TR 90UV transparent; housing: PC/ABS black; Coloured surround: PC/ABS green
Displays / operating elements			
Display		switching status	8 x LED, red
		operation	8 x LED, green
Accessories			
Accessories (optional)			surround in different colours
Remarks			
Pack quantity			1 pcs.

KT5005


Capacitive touch sensor

KTRSHMK-RBPKG/AM/2M

Electrical connection

Cable: 2 m, PUR

Connection



1	brown
3	blue
4	black