
EVW103

Connection cable


VDOGF040SCS00,6T04STGF040SCS



Application		
Special feature		Free from silicone; Halogen-free; Gold-plated contacts; Drag chain suitability
Application		welding applications
Free from silicone		yes
Electrical data		
Operating voltage	[V]	< 50 AC / < 60 DC
Protection class		III
Max. current load total	[A]	3
Operating conditions		
Ambient temperature	[°C]	-25...90
Note on ambient temperature		cULus: ...85
Ambient temperature (moving)	[°C]	-25...90
Note on ambient temperature (moving)		cULus: ...85
Protection		IP 65; IP 67; IP 68; IP 69K
Mechanical data		
Weight	[g]	35.1
Moulded-body material		TPU
Material nut		brass, anti-spatter
Sealing material		FKM
Drag chain suitability		yes
Drag chain suitability	bending radius for flexible use	min. 10 x cable diameter
	travel speed	max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s²
	bending cycles	> 2 Mio.
	torsional strain	± 180 °/m
Remarks		
Remarks		without label holders
Pack quantity		1 pcs.

Electrical connection - plug

Connector: 1 x M8, straight; coding: A; Contacts: 4, gold-plated; Moulded body: TPU, orange; Locking: brass, anti-spatter; Tightening torque: 0.3...0.5 Nm



EVW103


Connection cable

VDOGF040SCS00,6T04STGF040SCS

Electrical connection


Cable: 0.6 m, PUR, Halogen-free, grey, Ø 4.5 mm; not irradiated (can be recycled); resistant to welding sparks; 4 x 0.25 mm² (32 x Ø 0.1 mm)

Connection




Electrical connection - socket

Connector: 1 x M8, straight; coding: A; Contacts: 4, gold-plated; Moulded body: TPU, orange; Locking: brass, anti-spatter; Sealing: FKM; Tightening torque: 0.3...0.5 Nm



Diagrams and graphs

characteristic line for derating



1 Current [A]

2 Ambient temperature [°C]