
LMT102

Sensor for point level detection

LMCCE-A12E-QSKG-2/US



1 Tightening torque 20...25 Nm

ACS CRN EC 1935/2004 EHEDG Certified FCM CN FCM JP IO-Link KTW/W270

Product characteristics			
Number of inputs and outputs		Number of digital outputs: 2	
Factory setting		hydrous media	
Process connection		threaded connection G 1/2 sealing cone	
Application			
Special feature		Gold-plated contacts	
Media		liquid and viscous media; powder	
Recommended media		water; hydrous media; oils; oil-based media; powder	
Cannot be used for		See the operating instructions, chapter "Function and features".	
Probe length	[mm]	38	
Tank pressure		-1...40; (MAWP for applications according to CRN: 40 bar / 4 MPa) bar	-0.1...4; (MAWP for applications according to CRN: 40 bar / 4 MPa) MPa
Oil			
Medium temperature	[°C]	-20...100	
Medium temperature short time	[°C]	-20...150; (1 h)	
Water			
Medium temperature	[°C]	-20...100	
Medium temperature short time	[°C]	-20...150; (1 h)	
Electrical data			
Operating voltage	[V]	18...30 DC	
Current consumption	[mA]	< 50	
Protection class		III	
Reverse polarity protection		yes	
Measuring principle		capacitive	
Inputs / outputs			
Number of inputs and outputs		Number of digital outputs: 2	

LMT102

Sensor for point level detection

LMCCE-A12E-QSKG-2/US

Outputs			
Total number of outputs		2	
Output signal		switching signal; IO-Link	
Electrical design		PNP/NPN	
Number of digital outputs		2	
Output function		normally open / normally closed; (parameterisable)	
Max. voltage drop switching output DC	[V]	2.5	
Permanent current rating of switching output DC	[mA]	100	
Short-circuit protection		yes	
Type of short-circuit protection		pulsed	
Overload protection		yes	
Measuring/setting range			
Factory setting		hydrous media	
Response times			
Response time	[s]	< 0.5	
Interfaces			
Communication interface		IO-Link	
Transmission type		COM2 (38,4 kBaud)	
IO-Link revision		1.1	
SDCI standard		IEC 61131-9	
Profiles		Smart Sensor - SSP 0	Generic Profiled Sensor
		Function	Device identification
		Function	Process data variable
SIO mode		yes	
Required master port type		A	
Process data analogue		1	
Process data binary		2	
Min. process cycle time	[ms]	2.3	
Supported DeviceIDs		**Type of operation**	**DeviceID**
		default	370
Operating conditions			
Ambient temperature	[°C]	-20...85	
Note on ambient temperature		Medium temperature: < 100 °C	
		-20...60 °C	
		Medium temperature: < 150 °C	
Storage temperature	[°C]	-40...85	
Protection		IP 68; IP 69K	
Tests / approvals			
EMC		DIN EN 61000-6-2	
		DIN EN 61000-6-4	: open tanks
		DIN EN 61000-6-3	: closed tanks
Shock resistance		DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance		DIN EN 60068-2-6	20 g (10...2000 Hz)

LMT102

Sensor for point level detection

LMCCE-A12E-QSKG-2/US

MTTF	[years]	223	
UL approval		UL approval no.	H001

Mechanical data

Weight	[g]	202	
Dimensions	[mm]	Ø 30 / L = 125	
Materials		stainless steel (316L/1.4404); PEEK; PEI; FKM	
Materials (wetted parts)		PEEK surface characteristics: Ra < 0,8 µm / Rz = 4 µm	
Process connection		threaded connection G 1/2 sealing cone	

Displays / operating elements

Display		switching status	LED, yellow
		operating status	LED, green

Remarks


Pack quantity		1 pcs.	

Electrical connection

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



Connection



OUT1:	switching output IO-Link Teach
OUT2:	switching output
	colours to DIN EN 60947-5-2
	Core colours :
BK =	black
BN =	brown
BU =	blue
WH =	white