
DX2041

Multifunction display for monitoring analogue standard signals

DISPLAY/AX460/AC/DC



Product characteristics		
Housing		rectangular
Dimensions	[mm]	48 x 112 x 116
Application		
Application		displaying and monitoring analogue signals; e.g. pressure sensors, temperature sensors or flow sensors
Electrical data		
Frequency AC	[Hz]	50...60
Operating voltage	[V]	115...230 AC / 18...30 DC
Current consumption	[mA]	100
Inputs / outputs		
Number of inputs and outputs		Number of analogue inputs: 2
Inputs		
Number of analogue inputs		2; (Spannungs- oder Stromeingang)
Analogue input (current)	[mA]	0...20
Analogue input (voltage)	[V]	-10...10
Resolution of analogue input		16 bit
Precision analogue input	[%]	0,1
Operating conditions		
Ambient temperature	[°C]	-20...60
Storage temperature	[°C]	-25...70
Protection		IP 65
Protection rating terminals		IP 20
Tests / approvals		
EMC		EN 61000-6-2
		EN 61000-6-3
		EN 61000-6-4
Mechanical data		
Weight	[g]	351
Housing		rectangular
Type of mounting		installation in panels or panel cutouts; (panel cutout: 91 x 43 mm)

DX2041


Multifunction display for monitoring analogue standard signals

DISPLAY/AX460/AC/DC

Dimensions	[mm]	48 x 112 x 116	
Materials		housing: Noryl UL94-V-0	
Displays / operating elements			
Display		colour display	full graphic LCD display, touch screen
Remarks			
Pack quantity		1 pcs.	
Electrical connection			

screw terminals:

Connection



NC not used