


SMF550



Magnetic-inductive flow meter

SMG65KGFFRKG/UST

A suitable process adapter and a seal are also required to set up the sensor.
The right products can be found in the accessories section.



Product characteristics				
Measuring range	20...2000 l/min	1.2...120 m³/h	5.28...528.4 gpm	0.33...32.8 ft/s
Nominal diameter	DN65 (2 1/2")			
Process connection	ifm-specific device flange			
Application				
Special feature	gold-plated contacts			
Application	food and beverage industry			
Media	Conductive liquids; water; water-based media			
Note on media	food products such as beer, milk, fruit juices, soft drinks, ketchup, yogurt, yogurt toppings, ice cream			
	conductivity: ≥ 5 µS/cm			
Medium temperature	[°C]	-20...150		
Min. burst pressure	37.5 bar	543.75 psi	3.75 MPa	
Pressure rating	25 bar	362.5 psi	2.5 MPa	
Electrical data				
Operating voltage	[V]	18...32 DC		
Current consumption	[mA]	250; (24V)		
Protection class		III		
Reverse polarity protection		yes		

SMF550



Magnetic-inductive flow meter

SMG65KGFFRKG/UST

Power-on delay time	[s]	< 5			
Measuring principle		magnetic-inductive			
Inputs / outputs					
Total number of inputs and outputs		2			
Inputs					
Inputs		OUT2	external totalizer reset		
Outputs					
Total number of outputs		2			
Output signal		OUT1	pulse signal; totalizer switching signal; diagnostic signal; IO-Link		
		OUT2	analog signal; pulse signal; totalizer switching signal; diagnostic signal		
Electrical design		PNP/NPN			
Pulse output		flow rate meter			
Short-circuit protection		yes			
Type of short-circuit protection		yes (non-latching)			
Overload protection		yes			
Analog					
Number of analog outputs		1			
Analog current output	[mA]	4...20; (skalierbar)			
Max. load	[Ω]	500			
Resolution of analog output		0.38 μA			
Digital					
Number of digital outputs		2			
Max. voltage drop switching output DC	[V]	2			
Permanent current rating of switching output DC	[mA]	100			
Switching frequency DC	[Hz]	0...10000			
Measuring/setting range					
Measuring range		20...2000 l/min	1.2...120 m³/h	5.28...528.4 gpm	0.33...32.8 ft/s
Note on factory setting		0...30,0 m³/h			
Analog start point ASP		-2000...1600 l/min	-120...96 m³/h	-528.4...422.72 gpm	-32.8...26.24 ft/s
Analog end point AEP		-1600...2000 l/min	-96...120 m³/h	-422.72...528.4 gpm	-26.24...32.8 ft/s
Low flow cut-off LFC		0...1600 l/min	0...96 m³/h	0...422.72 gpm	0...26.24 ft/s
Pulse length	[s]	0.00005...2			
Pulse value		0.004...99999000 l			
Temperature monitoring					
Measuring range		-20...150 °C		-4...302 °F	
Analog start point		-20...116 °C		-4...240.8 °F	
Analog end point		14...150 °C		57.2...302 °F	
Conductivity monitoring					
Measuring range	[μS/cm]	100...100000			
Resolution	[μS/cm]	1			

SMF550



Magnetic-inductive flow meter

SMG65KGFFRKG/UST

Analog start point	[μS/cm]	0...80000
Analog end point	[μS/cm]	20000...100000
Accuracy / deviations		
Volumetric flow monitoring		
Accuracy (under reference conditions)	with optional factory calibration (availability is being planned)	± (0,2 % MW + 2 mm/s)
	standard	± (0,5 % MW + 1,5 mm/s)
Repeatability		0,1% MW
Temperature monitoring		
Accuracy	[K]	± 1 (v > 0,5 m/s)
Repeatability	[K]	± 0,5 (v > 0,5 m/s)
Conductivity monitoring		
Accuracy (in the measuring range)	in the range of 100...20000 μS/cm	±10% MW
	in the range of 20000...100000 μS/cm	±20% MW
Repeatability		± 5% MW
Reaction times		
Volumetric flow monitoring		
Response time	[s]	< 0.3
Damping process value dAP	[s]	0...5
Temperature monitoring		
Response time	[s]	< 3; (v > 0,5 m/s)
Conductivity monitoring		
Response time	[s]	< 2
Software / programming		
Diagnostic functions		direction of flow detection; liquid detection
Interfaces		
Communication interface		IO-Link
Transmission type		COM3 (230,4 kBaud)
IO-Link revision		1.1.3
SDCI standard		IEC 61131-9
Profiles	Smart Sensor - SSP 4.3.4	Measuring and Switching Sensor, floating point, 4 channel
	BLOB	Binary Large Object transfer
	Common - I&D	Identification and Diagnosis
	Extension	Sensor Control Wide
	Extension	Quantity detection, switches when value exceeds the setpoint
	Function	Locator
	Function	ProductURI
SIO mode		yes
Required master port class		A
Process data analog		6
Process data binary		8
Min. process cycle time	[ms]	1.9

SMF550



Magnetic-inductive flow meter

SMG65KGFFRKG/UST

IO-Link process data (cyclical)	Function	bit length
	totalizer	32
	flow	32
	temperature	32
	conductivity	32
	status	4
	binary switching information	8
IO-Link functions (acyclical)	direction of flow detection; totalizer; memory; operating hours counter; internal temperature; simulation function	
Supported DeviceIDs	Type of operation	DeviceID
	default	1797

Operating conditions		
Ambient temperature	-20...65 °C	-4...149 °F
Storage temperature	-20...80 °C	-4...176 °F
Protection	IP 67; IP 69; (to DIN EN 60529)	

Tests / approvals		
EMC	DIN 61326-1	
CPA approval	model number	SMF
	accuracy class	0,5
Shock resistance	DIN IEC 68-2-27	20 g (18ms)
Vibration resistance	DIN IEC 68-2-6	5 g (10...2000Hz)
MTTF [years]		82
UL approval	UL approval number	I032
Pressure equipment directive	sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	

Mechanical data		
Weight [g]		6979
Housing		tubular
Inlet pipe length		5 x DN
Outlet pipe length		2 x DN
Dimensions [mm]		Ø 154 / L = 140
Material	housing: stainless steel (1.4404 / 316L); flange: stainless steel (1.4301 / 304); electronics fixture: stainless steel (1.4301 / 304); electronics: stainless steel (1.4404 / 316L); LED ring: PP	
Materials (wetted parts)	Pipe section: PFA; electrodes: stainless steel (1.4435 / 316L)	
Nominal diameter		DN65 (2 1/2")
Process connection		ifm-specific device flange
Surface characteristics Ra/Rz of the wetted parts		Ra < 0.4 µm

Displays / operating elements		
Display	operating status	LED ring, three-color
Factory setting		m³/h; °C; µS/cm

SMF550



Magnetic-inductive flow meter

SMG65KGFFRKG/UST


Remarks	
Remarks	MW = Measured value
	MEW = Final value of the measuring range
	pulse and totalizer signal are only available for one of the two outputs
	reference conditions (1/2): water (free of gas bubbles), 15...35 °C, process connection: DIN32676 series A, pipe standard suitable for process connection
	reference conditions (2/2): inlet pipe length 10xDN, outlet pipe length 5xDN, device settling time: 30 minutes, device orientation: horizontal, display orientation: up
Notes	accuracy specifications according to factory certificate on delivery
Pack quantity	A suitable process adapter and a seal are also required to set up the sensor.; The right products can be found in the accessories section.
	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



Connection



Electrical connection - plug

1	L+	
2	MP2	DO2, AO, Reset
3	L-	
4	MP1	DO1, IO-Link

AO: analog output; DO: digital output; MP: multi-function connection