


KB5062



Capacitive sensor

KB-3020-BPKG/NI/US-100-DPS




Product characteristics	
Electrical design	PNP
Output function	normally open
Sensing range [mm]	20
Housing	tubular
Dimensions [mm]	Ø 34 / L = 93
Electrical data	
Operating voltage [V]	10...36 DC
Current consumption [mA]	13; (24 V)
Protection class	II
Reverse polarity protection	yes
Outputs	
Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	40
Short-circuit proof	yes
Overload protection	yes
Monitoring range	
Sensing range [mm]	20
Sensing range adjustable	yes
Factory setting sensing range [mm]	20
Real sensing range Sr [mm]	20 ± 10 %
Operating distance [mm]	0...16.2
Accuracy / deviations	
Correction factor	glass: 0.4 / water: 1 / ceramics: 0.2 / PVC: 0.2
Hysteresis [% of Sr]	1...15
Switch-point drift [% of Sr]	-15...15

KB5062



Capacitive sensor

KB-3020-BPKG/NI/US-100-DPS

Operating conditions		
Ambient temperature	[°C]	-25...70
Protection		IP 65
Increased immunity		yes; (Increased immunity to conducted radio frequency interference)
Tests / approvals		
EMC		EN 60947-5-2
MTTF	[years]	778
Mechanical data		
Weight	[g]	169.5
Housing		tubular
Mounting		non-flush mountable
Dimensions	[mm]	Ø 34 / L = 93
Material		housing: PBT
Displays / operating elements		
Display	Switching status	1 x LED, yellow
Accessories		
Items supplied		Mounting clamp: 2 cylinder screws: 2 spring discs: 2
Remarks		
Pack quantity		1 pcs.
Electrical connection - plug		
Connector: 1 x M12; coding: A; Contacts: 4		
		
Connection		
