
UGT581

Ultrasonic sensor

UGQ00300E2KG/US



1 LED echo
2 LED switching status
3 teach button

Product characteristics		
Electrical design		PNP
Output function		normally open / normally closed; (parameterisable)
Sensing range	[mm]	40...300; (Target: 100 x 100 mm)
Housing		rectangular with M18 thread
Dimensions	[mm]	53 x 20 x 37.7
Electrical data		
Operating voltage	[V]	10...30 DC; ("supply class 2" to cULus)
Current consumption	[mA]	< 35
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	< 0.3
Converter frequency	[kHz]	300
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 1; Number of analogue outputs: 1
Outputs		
Total number of outputs		2
Output signal		switching signal; analogue signal
Electrical design		PNP
Number of digital outputs		1
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2.2
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	8
Number of analogue outputs		1

UGT581

Ultrasonic sensor

UGQ00300E2KG/US

Analogue voltage output	[V]	0...10
Min. load resistance	[Ω]	3000
Short-circuit protection		yes
Overload protection		yes
Detection zone		
Sensing range	[mm]	40...300; (Target: 100 x 100 mm)
Blind zone	[mm]	40
Angle of aperture cylindrical	[°]	15; (±2)
Detection range hysteresis	[mm]	< 1
Max. deviation from the 90° angle sensor/object	[°]	± 4
Accuracy / deviations		
Temperature compensation		yes
Hysteresis	[%]	< 1
Switch point drift	[%]	-5...5
Linearity error of analogue output	[%]	≤ 1
Repeatability		1 %
Resolution	[mm]	2
Notes on the accuracy / deviation		The indicated values are reached after a warm-up time of min. 20 minutes
Response times		
Response time	[ms]	< 450; (analogue output)
Operating conditions		
Ambient temperature	[°C]	-20...70
Storage temperature	[°C]	-30...80
Protection		IP 67
Tests / approvals		
EMC		EN 61000-4-2 ESD: 4 kV CD / 8 kV AD
		EN 61000-4-3 HF radiated: 3 V/m
		EN 61000-4-4 Burst: 2 kV
		EN 61000-4-6 HF conducted: 3 V
		EN 55011: Class A
Vibration resistance		EN 60068-2-6 Fc: (10-55) Hz 1 mm amplitude, oscillation period 5 min., 30 min. per axis at resonance or 55 Hz
Shock resistance		EN 60068-2-27 Ea: 30 g 11 ms half-sine; 3 shocks each in every direction of the 3 coordinate axes
MTTF	[years]	191
UL approval		Ta: -20...70 °C
		voltage supply: Class 2
		File number UL: E174191
Mechanical data		
Weight	[g]	98.5
Housing		rectangular with M18 thread
Dimensions	[mm]	53 x 20 x 37.7

UGT581

Ultrasonic sensor


UGQ00300E2KG/US

Thread designation			M18 x 1
Materials			stainless steel (630/1.4542/17-4 PH); PBT; PA; epoxy glass ceramics
Tightening torque	[Nm]		50
Displays / operating elements			
Display		switching status	1 x LED, yellow
		echo	1 x LED, green
Teach function			yes
Accessories			
Items supplied			lock nuts: 1 x M18, stainless steel
Remarks			
Remarks			operating voltage "supply class 2" according to cULus
Pack quantity			1 pcs.
Electrical connection			

Connector: 1 x M12; coding: A; Contacts: 4



Connection





UGT581

Ultrasonic sensor

UGQ00300E2KG/US

Diagrams and graphs





1: distance

2: Detection zone

3: switch-on/switch-off graph

4: Target 100 x 100 mm

5: 50% of the target in the detection zone

6: switch point