
AC6002

IO-Link master with AS-i interface

IO-Link Master AS-i 2P IP67



Application		
Application		field installation
Loop-through function		voltage supply; fieldbus interface
Electrical data		
Operating voltage	[V]	26...31.6 DC; (AS-i)
Max. current consumption from AS-i	[mA]	350
Protection class		III
Max. current load total	[A]	0.3; (ports 1+2: 0,3 (AS-i))
Inputs / outputs		
Total number of inputs and outputs		4; (configurable)
Number of inputs and outputs		Number of digital inputs: 4; Number of digital outputs: 2
Inputs		
Number of digital inputs		4; (IO-Link Port Class A: 2 x 2)
Sensor supply of the inputs		AS-i
Switching level high	[V]	11...30
Switching level low	[V]	0...5
Digital inputs protected against short circuits		yes
Outputs		
Number of digital outputs		2; (IO-Link Port Class A: 2 x 1)
Total current rating of all outputs	[A]	0.3

AC6002

IO-Link master with AS-i interface

IO-Link Master AS-i 2P IP67

Short-circuit proof		yes	
Actuator supply outputs		AS-i	
Interfaces			
Communication interface		IO-Link; AS-i	
IO-Link Master			
Transmission type		COM1 (4,8 kBaud); COM2 (38,4 kBaud); COM3 (230,4 kBaud)	
IO-Link revision		1.1	
Number of ports class A		2	
Operating conditions			
Ambient temperature	[°C]	-25...60	
Storage temperature	[°C]	-25...85	
Max. relative air humidity	[%]	90	
Protection		IP 65; IP 66; IP 67	
Protection rating (NEMA 250)		6P	
Pollution degree		2	
Chemical media		ISO 16750-5	AA, BA, BD, HLP, CC, DB, DC, DD, CA
		NEMA 250 5.13.1	AA
Tests / approvals			
EMC		EN 61000-6-2	
		EN 61000-6-4	
Shock resistance		DIN EN 60068-2-27	
Vibration resistance		DIN EN 60068-2-64 2009-04	
		DIN EN 60068-2-6 2008-10	
MTTF	[years]	194	
AS-i classification			
AS-i version		2.11; 3.0	
Extended addressing mode		no	
AS-i profile		additional slave (CTT1 input)	S-7.3.E
AS-i profile		additional slave (CTT1 output)	S-7.3.2
AS-i profile		basic slave (CTT1 input)	S-7.4.E
Number of AS-i devices		1...5	
Mechanical data			
Weight	[g]	235.7	
Housing		rectangular	
Type of mounting		backplane mounting	
Dimensions	[mm]	124 x 59.3 x 38.4	
Materials		housing: PA orange; socket: brass nickel-plated	
Electrical connection			
Module connection		M12	
Remarks			
Remarks		For further information please see the operating instructions.	
Pack quantity		1 pcs.	


AC6002

IO-Link master with AS-i interface

IO-Link Master AS-i 2P IP67

Electrical connection - IO-Link

Connector: 2 x M12; coding: A; Contacts: 4



IO-Link Port Class A X01...X02

1	+ 24 V DC (AS-i)
2	digital input
3	GND (AS-i)
4	C/Q IO-Link
5	not used

Electrical connection - voltage supply IN

Connector: 1 x M12; coding: A; Contacts: 4




X21

1	AS-i +
2	AUX - bridged
3	AS-i -
4	AUX + bridged

Electrical connection - voltage supply OUT

Connector: 1 x M12; coding: A; Contacts: 4



X22

1	AS-i +
2	AUX - bridged
3	AS-i -
4	AUX + bridged
5	not used