


TS2069



Temperature cable sensor with process connection

TS-200KLD10-...../US/



Product characteristics

Measuring range	-40...90 °C	-40...194 °F
Process connection	Clamp fitting Ø 10 mm	
Installation length EL [mm]	42	

Application

Special feature	gold-plated contacts	
Measuring element	1 x Pt 1000; (to DIN EN 60751, class A)	
Media	liquids and gases	
Pressure rating	160 bar	16 MPa
Minimum installation depth [mm]	15	

Electrical data

Protection class	III
------------------	-----

Measuring/setting range

Measuring range	-40...90 °C	-40...194 °F
-----------------	-------------	--------------

Accuracy / deviations

Accuracy [K]	$\pm (0,15 K + 0,002 x t)$
--------------	-----------------------------

Reaction times

Dynamic response T05 / T09 [s]	6 / 25; (according to DIN EN 60751)
--------------------------------	-------------------------------------

Operating conditions

Protection	IP 67
------------	-------

Tests / approvals

MTTF [years]	11416
--------------	-------

Mechanical data

Weight [g]	98
Housing	tubular
Design	Measuring probes
Dimensions [mm]	Ø 10 / L = 50
Material	stainless steel
Materials (wetted parts)	stainless steel (1.4404 / 316L)
Process connection	Clamp fitting Ø 10 mm
Probe diameter [mm]	10
Installation length EL [mm]	42

TS2069



Temperature cable sensor with process connection

TS-200KDKD10-...../US/

Remarks	
Remarks	The values for accuracy apply to flowing water.
Pack quantity	1 pcs.

Electrical connection

Cable: 2 m, PUR

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



Connection

