
AC507S

Safe AS-Interface ClassicLine module with quick mounting technology

ClassicL 2SI 2DOT 2LO OSSD



Application		
Design		housing for DIN rail mounting
Application		AS-i Safety at Work
Electrical data		
Operating voltage	[V]	26.5...31.6 DC; ("supply class 2" to cULus)
Max. current consumption from AS-i	[mA]	280
Protection class		III
Reverse polarity protection		yes; (AS-i)
Reverse polarity protection		yes
Max. current load per module/slot	[A]	0.2
Integrated watchdog		yes
Inputs / outputs		
Number of inputs and outputs		Number of digital inputs: 2; Number of digital outputs: 2
Inputs		
Number of digital inputs		2; (2 x safety input)
Input circuit of digital inputs		PNP
Sensor supply of the inputs		AS-i
Voltage supply	[V]	19.2...30
Max. total current rating of inputs	[mA]	200
Input current limitation	[mA]	8
Input current High	[mA]	> 6
Input current Low	[mA]	< 2

AC507S

Safe AS-Interface ClassicLine module with quick mounting technology

ClassicL 2SI 2DOT 2LO OSSD

Switching level high	[V]	> 11
Switching level low	[V]	< 5
Overload protection digital inputs		yes
Short-circuit detection		yes
Cross-fault monitoring		no
Short-circuit proof		yes
Outputs		
Output signal		switching signal
Number of digital outputs		2
Voltage range DC	[V]	18...28.8; (AS-i)
Max. current load per output	[mA]	50
Short-circuit protection		yes
Short-circuit proof		yes
Overload protection		yes
Electrically separated		no
Actuator supply outputs		AS-i
Operating conditions		
Ambient temperature	[°C]	-25...55
Note on ambient temperature		with switched outputs: -25...40 °C
Max. relative air humidity	[%]	95
Max. height above sea level	[m]	2000
Protection		IP 67
Pollution degree		2
Tests / approvals		
EMC		EN 62026-2
		EN 61326-3-1
Shock resistance		EN 60068-2-27
Vibration resistance		EN 60068-2-6
Safety classification		
Complies with the requirements		ISO 13849-1 category 4, PL e
		IEC 61508 SIL 3
Mission time TM (additional indication)		20 years
PFH	[1/h]	2,33E-11
AS-i classification		
AS-i version		2.11; 3.0
AS-i addressing		addressing socket
Extended addressing mode		no
AS-i master profile		M3; M4
AS-i profile		S-7.B.E
AS-i I/O configuration	[hex]	7
AS-i ID code	[hex]	B.E
AS-i certificate		126301

AC507S

Safe AS-Interface ClassicLine module with quick mounting technology

ClassicL 2SI 2DOT 2LO OSSD

Assignment of the data bits	data bit	D0	D1	D2	D3
	assignment	O1	O2	O3	O4

Mechanical data		
Weight	[g]	321.3
Housing		rectangular
Type of mounting		AS-i flat cables directly connectable; mounting on DIN rail; (TH35 (EN 60715))
Dimensions	[mm]	103 x 45 x 44.7
Materials		housing: PA; piercing contacts: CuSn6 nickel-plated and tin-plated

Displays / operating elements		
Display	operation	1 x LED, green
	errors	1 x LED, red
	switching status	1 x LED, yellow
	alarm	1 x LED, red

Electrical connection	
Module connection	Flat cables

Accessories	
Items supplied	lower part
Accessories (optional)	Addressing cable:, E70213
	Protective cap: M12, E73004


Remarks	
Remarks	PL e, cat. 4, SIL 3 only if the fault exclusions described in the manual are used
Pack quantity	1 pcs.

Electrical connection

quick mounting technology for AS-i flat cable: ; three orientations possible

Electrical connection - O-3/4


Connector: 1 x M12; coding: A; Contacts: 3; Maximum cable length: 10 m



1	n.c.	
2		O-4
3 (l-)	L-	
4		O-3
5	n.c.	

Electrical connection - O-4

Connector: 1 x M12; coding: A; Contacts: 2; Maximum cable length: 10 m



1	n.c.	
2	n.c.	
3 (l-)	L-	
4		O-4
5	n.c.	


AC507S

Safe AS-Interface ClassicLine module with quick mounting technology

ClassicL 2SI 2DOT 2LO OSSD

Electrical connection - SI-1/2


Connector: 1 x M12; coding: A; Contacts: 5; Maximum cable length: 10 m



1 (l+)	L+	
2		SI-2
3 (l-)	L-	
4		SI-1
5		FE

Electrical connection - Trans

Connector: 1 x M12; coding: A; Contacts: 5; Maximum cable length: 10 m



1 (l+)	L+	
2 (l-)	L-	
3 (l-)	L-	
4 (l+)	L+	
5		FE

FE: functional earth; n.c.: not used