




Inductive high-temperature sensor

I9-3020ZBPKG/M50/5M/SH



Product characteristics	
Electrical design	PNP
Output function	normally open
Sensing range [mm]	20
Housing	threaded type
Dimensions [mm]	M50 x 1.5 / L = 70
Application	
Application	high-temperature applications
Electrical data	
Operating voltage [V]	10...35 DC
Current consumption [mA]	< 15
Protection class	III
Reverse polarity protection	yes
Outputs	
Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	150
Switching frequency DC [Hz]	100
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes
Detection zone	
Sensing range [mm]	20
Operating distance [mm]	0...16.2
Accuracy / deviations	
Correction factor	steel: 1 / stainless steel: 0.6 / brass: 0.3 / aluminium: 0.2 / copper: 0.1
Hysteresis [% of Sr]	3...15



Inductive high-temperature sensor

I9-3020ZBPKG/M50/5M/SH

Switch point drift	[% of Sr]	-10...10
--------------------	-----------	----------

Operating conditions

Ambient temperature	[°C]	0...180
Protection		IP 65

Tests / approvals

EMC	EN 61000-4-2 ESD	2 kV CD / 4 kV AD
	EN 61000-4-3 HF radiated	3 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	3 V
MTTF	[years]	700

Mechanical data

Weight	[g]	560.5
Housing		threaded type
Mounting		flush mountable
Dimensions	[mm]	M50 x 1.5 / L = 70
Thread designation		M50 x 1.5
Materials		housing: stainless steel; sensing face: LCP

Accessories

Items supplied		lock nuts: 2
----------------	--	--------------


Remarks

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection

Cable: 5 m, silicone; highly flexible; 3 x 0.22 mm²

Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue