


SMF850



Magnetic-inductive flow meter

SMGX1KGFFRKG/UST

A suitable process adapter and a seal are also required to set up the sensor.
The right products can be found in the accessories section.



Product characteristics				
Measuring range	75...7500 l/min	4.5...450 m³/h	20...1981 gpm	0.33...33.42 ft/s
Nominal diameter	DN125 (5")			
Process connection	ifm-specific device flange			
Application				
Special feature	gold-plated contacts			
Application	food and beverage industry			
Media	Conductive liquids; water; water-based media			
Note on media	food products such as beer, milk, fruit juices, soft drinks, ketchup, yogurt, yogurt toppings, ice cream			
	conductivity: ≥ 5 µS/cm			
Medium temperature	-20...150 °C]			
Min. burst pressure	24 bar	348 psi	2.4 MPa	
Pressure rating	16 bar	232 psi	1.6 MPa	

SMF850



Magnetic-inductive flow meter

SMGX1KGFFRKG/UST

Electrical data				
Operating voltage	[V]	18...32 DC		
Current consumption	[mA]	250; (24V)		
Protection class		III		
Reverse polarity protection		yes		
Power-on delay time	[s]	< 5		
Measuring principle		magnetic-inductive		
Inputs / outputs				
Total number of inputs and outputs		2		
Inputs				
Inputs		OUT2	external totalizer reset	
Outputs				
Total number of outputs		2		
Output signal		OUT1	pulse signal; totalizer switching signal; diagnostic signal; IO-Link	
		OUT2	analog signal; pulse signal; totalizer switching signal; diagnostic signal	
Electrical design		PNP/NPN		
Pulse output		flow rate meter		
Short-circuit protection		yes		
Type of short-circuit protection		yes (non-latching)		
Overload protection		yes		
Analog				
Number of analog outputs		1		
Analog current output	[mA]	4...20; (skalierbar)		
Max. load	[Ω]	500		
Resolution of analog output		0.38 μA		
Digital				
Number of digital outputs		2		
Max. voltage drop switching output DC	[V]	2		
Permanent current rating of switching output DC	[mA]	100		
Switching frequency DC	[Hz]	0...10000		
Measuring/setting range				
Measuring range		75...7500 l/min	4.5...450 m³/h	20...1981 gpm
Note on factory setting		0...110,0 m³/h		
Analog start point ASP		-7500...6000 l/min	-450...360 m³/h	-1981...1585 gpm
Analog end point AEP		-6000...7500 l/min	-360...450 m³/h	-1585...1981 gpm
Low flow cut-off LFC		0...6000 l/min	0...360 m³/h	0...1585 gpm
Pulse length	[s]	0.00005...2		
Pulse value		0.013...99999000 l		
Temperature monitoring				
Measuring range		-20...150 °C		-4...302 °F

SMF850



Magnetic-inductive flow meter

SMGX1KGFFRKG/UST

Analog start point		-20...116 °C	-4...240.8 °F
Analog end point		14...150 °C	57.2...302 °F
Conductivity monitoring			
Measuring range	[μS/cm]	100...100000	
Analog start point	[μS/cm]	0...80000	
Analog end point	[μS/cm]	20000...100000	
Accuracy / deviations			
Volumetric flow monitoring			
Accuracy (in the measuring range)		with optional factory calibration (availability is being planned)	± (0,2 % MW + 2 mm/s)
		standard	± (0,5 % MW + 1,5 mm/s)
Repeatability		0,1% MW	
Temperature monitoring			
Accuracy	[K]	± 1 (v > 0,5 m/s)	
Repeatability	[K]	± 0,5 (v > 0,5 m/s)	
Conductivity monitoring			
Accuracy (in the measuring range)		in the range of 100...20000 μS/cm	±10% MW
		in the range of 20000...100000 μS/cm	±20% MW
Repeatability		± 5% MW	
Reaction times			
Volumetric flow monitoring			
Response time	[s]	< 0.3	
Damping process value dAP	[s]	0...5	
Temperature monitoring			
Response time	[s]	< 3; (v > 0,5 m/s)	
Conductivity monitoring			
Response time	[s]	< 2	
Software / programming			
Diagnostic functions		direction of flow detection; liquid detection	
Interfaces			
Communication interface		IO-Link	
Transmission type		COM3 (230,4 kBaud)	
IO-Link revision		1.1.3	
SDCI standard		IEC 61131-9	
Profiles		Smart Sensor - SSP 4.3.4	Measuring and Switching Sensor, floating point, 4 channel
		BLOB	Binary Large Object transfer
		Common - I&D	Identification and Diagnosis
		Extension	Sensor Control Wide
		Extension	Quantity detection, switches when value exceeds the setpoint
		Function	Locator
		Function	ProductURI
SIO mode		yes	
Required master port class		A	

SMF850



Magnetic-inductive flow meter

SMGX1KGFFRKG/UST

Process data analog	6														
Process data binary	8														
Min. process cycle time [ms]	1.9														
IO-Link process data (cyclical)	<table> <tr> <th>Function</th><th>bit length</th></tr> <tr> <td>totalizer</td><td>32</td></tr> <tr> <td>flow</td><td>32</td></tr> <tr> <td>temperature</td><td>32</td></tr> <tr> <td>conductivity</td><td>32</td></tr> <tr> <td>status</td><td>4</td></tr> <tr> <td>binary switching information</td><td>8</td></tr> </table>	Function	bit length	totalizer	32	flow	32	temperature	32	conductivity	32	status	4	binary switching information	8
Function	bit length														
totalizer	32														
flow	32														
temperature	32														
conductivity	32														
status	4														
binary switching information	8														
IO-Link functions (acyclical)	direction of flow detection; totalizer; memory; operating hours counter; internal temperature; simulation function														
Supported DeviceIDs	<table> <tr> <th>Type of operation</th><th>DeviceID</th></tr> <tr> <td>default</td><td>1806</td></tr> </table>	Type of operation	DeviceID	default	1806										
Type of operation	DeviceID														
default	1806														

Operating conditions		
Ambient temperature	-20...65 °C	-4...149 °F
Storage temperature	-20...80 °C	-4...176 °F
Protection	IP 67; IP 69; (to DIN EN 60529)	

Tests / approvals		
EMC	DIN 61326-1	
Shock resistance	DIN IEC 68-2-27	20 g (18ms)
Vibration resistance	DIN IEC 68-2-6	5 g (10...2000Hz)
MTTF [years]	83	
UL approval	UL approval number	I032
	File number UL	E174189
Pressure equipment directive	sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	

Mechanical data		
Weight [g]	15024	
Housing	tubular	
Inlet pipe length	5 x DN	
Outlet pipe length	2 x DN	
Dimensions [mm]	Ø 220.1 / L = 200	
Material	housing: stainless steel (1.4404 / 316L); flange: stainless steel (1.4301 / 304); electronics fixture: stainless steel (1.4301 / 304); electronics: stainless steel (1.4404 / 316L); LED ring: PP	
Materials (wetted parts)	Pipe section: PFA; electrodes: stainless steel (1.4435 / 316L)	
Nominal diameter	DN125 (5")	
Process connection	ifm-specific device flange	
Surface characteristics Ra/Rz of the wetted parts	Ra < 0.4 µm	

Displays / operating elements		
Display	operating status	LED ring, three-color
Factory setting	m³/h; °C; µS/cm	

SMF850



Magnetic-inductive flow meter

SMGX1KGFFRKG/UST


Remarks	
Remarks	MW = Measured value
	MEW = Final value of the measuring range
	pulse and totalizer signal are only available for one of the two outputs
	reference conditions (1/2): water (free of gas bubbles), 15...35 °C, process connection: DIN32676 series A, pipe standard suitable for process connection
	reference conditions (2/2): inlet pipe length 10xDN, outlet pipe length 5xDN, device settling time: 30 minutes, device orientation: horizontal, display orientation: up
Notes	accuracy specifications according to factory certificate on delivery
Pack quantity	A suitable process adapter and a seal are also required to set up the sensor.; The right products can be found in the accessories section.
	1 pcs.

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



Connection



1	L+	
2	MP2	DO2, AO, Reset
3	L-	
4	MP1	DO1, IO-Link

AO: analog output; DO: digital output; MP: multi-function connection