


AL4222



Ethernet module with EtherNet/IP interface

ETH Module SL EIP 8DO 8DI IP67



Application		
Application		I/O modules for field applications
Daisy-chain function		fieldbus interface
Electrical data		
Operating voltage	[V]	20...30 DC; (US ; to SELV/PELV)
Current consumption	[mA]	300...3900
Protection class		III
Additional voltage supply	[V]	20...30 DC; (UA)
Actuator supply UA		
Max. current load total	[A]	4
Current rating per port	[A]	3.6



Ethernet module with EtherNet/IP interface

ETH Module SL EIP 8DO 8DI IP67

Sensor supply US		
Max. current load total	[A]	3.6
Current rating per port	[A]	3.6
Inputs / outputs		
Number of inputs and outputs	Number of digital inputs: 8; Number of digital outputs: 8	
Inputs		
Number of digital inputs	8; (type 2 according to IEC 61131-2)	
Switching level high	[V]	11...30
Switching level low	[V]	0...5
Digital inputs protected against short circuits	yes	
Outputs		
Number of digital outputs	8	
Short-circuit proof	yes	
Actuator supply UA		
Max. current load per output	[mA]	3600
Software / programming		
Parameter setting options	Counter function	
Functions and parameters	Function	CTU (Up Counter), CTD (Down Counter), CTUD (Up-Down Counter), CTDIR (Direction Counter)
	switching function (SSC)	single point, two point, window, latch
	number	4 (1 counter for each input port)
	count frequency	4500 Hz
	main counter	32 Bit (0...4.294.967.295)
	batch counter	16 Bit (0...65.535)
Interfaces		
Communication interface	Ethernet	
Ethernet - EtherNet/IP		
Transmission standard	10Base-T; 100Base-TX	
Transmission rate	10 MBit/s; 100 MBit/s	
Protocol	EtherNet/IP	
Factory settings	IP address: 192.168.1.250	
	subnet mask: 255.255.255.0	
	gateway IP address: 0.0.0.0	
	MAC address: see type label	
Note on interfaces	DHCP, BOOTP, static	
	DLR (Device Level Ring)	
	Supported network topologies: line	
	ring	
Operating conditions		
Ambient temperature	[°C]	-25...60
Storage temperature	[°C]	-25...85
Max. relative air humidity	[%]	90
Protection	IP 65; IP 66; IP 67	



Ethernet module with EtherNet/IP interface

ETH Module SL EIP 8DO 8DI IP67

Protection rating (NEMA 250)	6P	
Pollution degree	2	
Chemical media	ISO 16750-5	AA, BA, BD, HLP, CC, DB, DC, DD, CA
	NEMA 250 5.13.1	AA

Tests / approvals

EMC	EN 61000-6-2	
	EN 61000-6-4	
Shock resistance	DIN EN 60068-2-27	
Vibration resistance	DIN EN 60068-2-64 2009-04	
	DIN EN 60068-2-6 2008-10	
MTTF [years]	70	

Mechanical data

Weight [g]	413.3	
Housing	rectangular	
Type of mounting	Backplane mounting	
Dimensions [mm]	208 x 59.3 x 38.4	
Material	housing: PA orange; Socket: brass nickel-plated	
Sealing material	FKM	

Remarks

Remarks	Further information is available in the manual.	
Pack quantity	1 pcs.	

Electrical connection - Ethernet

Connector: M12; coding: D; Contacts: 4; sealing: FKM




IN / OUT XF1, XF2

1:	TX +
2:	RX +
3:	TX -
4:	RX -
5:	n.c.

Electrical connection - inputs / outputs

Connector: M12; coding: A; Contacts: 5; sealing: FKM



Digital Output X1...X4

1:	n.c.
2:	OUT2 DO2 (UA)
3:	L - (UA)
4:	OUT1 DO1 (UA)
5:	FE

AL4222



Ethernet module with EtherNet/IP interface

ETH Module SL EIP 8DO 8DI IP67

Digital Input X5...X8

- | | |
|----|----------|
| 1: | L + (US) |
| 2: | IN2 DI2 |
| 3: | L - (US) |
| 4: | IN1 DI1 |
| 5: | FE |

Electrical connection - voltage supply IN

Connector: M12; coding: A; Contacts: 4



XD1

- | | |
|----|----------|
| 1: | L + (US) |
| 2: | L - (UA) |
| 3: | L - (US) |
| 4: | L + (UA) |