
SI6200

Flow monitor

SIS30ABBFPKG/US-100-IPF

Please do not use for new projects.
no more adapters available as accessories



1 LED bar display
2 setting pushbutton
3 Aseptoflex thread

EC 1935/2004 FCM CN FCM JP Hygienic Cleanable

Product characteristics			
Number of inputs and outputs		Number of digital outputs: 1	
Process connection		threaded connection Aseptoflex external thread Aseptoflex	
Application			
Special feature		Gold-plated contacts	
Application		hygienic systems	
Medium temperature	[°C]	-25...95; (for SIP process: ...140 °C)	
Pressure rating		30 bar	3 MPa
Electrical data			
Operating voltage	[V]	19...36 DC	
Current consumption	[mA]	< 60	
Min. insulation resistance	[MΩ]	100; (500 V DC)	
Protection class		III	
Reverse polarity protection		yes	
Power-on delay time	[s]	10	

SI6200

Flow monitor

SIS30ABBFPKG/US-100-IPF

Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 1
Outputs		
Total number of outputs		1
Output signal		switching signal
Electrical design		PNP
Number of digital outputs		1
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Measuring/setting range		
Probe length L	[mm]	38
Liquids		
Setting range	[cm/s]	3...300
Greatest sensitivity	[cm/s]	3...100
Gases		
Setting range	[cm/s]	200...3000
Greatest sensitivity	[cm/s]	200...800
Accuracy / deviations		
Repeatability	[cm/s]	1...5
Note on repeatability		for water 5...100 cm/s; 25 °C
		Factory setting
Temperature drift	[cm/s x 1/K]	0.1; (for water 5...100 cm/s; 10...70 °C)
Temperature gradient	[K/min]	300
Switch point accuracy	[cm/s]	± 2...± 10; (for water 5...100 cm/s; 25 °C; Factory setting)
Hysteresis	[cm/s]	2...5; (for water 5...100 cm/s; 25 °C; Factory setting)
Response times		
Response time	[s]	1...10
Software / programming		
Adjustment of the switch point		pushbutton
Operating conditions		
Ambient temperature	[°C]	-25...60
Protection		IP 67; IP 69K
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	10 V

SI6200

Flow monitor

SIS30ABBFPKG/US-100-IPF

Shock resistance		DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance		DIN EN 60068-2-6	10 g (55...2000 Hz)
MTTF	[years]	298	

Mechanical data

Weight	[g]	403.5
Housing		cylindrical
Dimensions	[mm]	Ø 50 / L = 137
Materials		stainless steel (316L/1.4404); PC; PBT-GF20; EPDM/X; O-ring: FKM
Materials (wetted parts)		stainless steel (316L/1.4435) surface characteristics: Ra < 0,4 µm / Rz = 4 µm
Process connection		threaded connection Aseptoflex external thread Aseptoflex
Probe diameter	[mm]	7.7
Installation length EL	[mm]	38

Displays / operating elements

Display	function	10 x LED, three-colour

Remarks

Notes	Please do not use for new projects.; no more adapters available as accessories
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



Connection

