
EVW167

Connecting cable with socket

ADOGH046SCS0002T04



Application			
Special feature		Free from silicone; Halogen-free; Gold-plated contacts; Drag chain suitability	
Application		welding applications	
Free from silicone		yes	
Electrical data			
Operating voltage	[V]	10...36 DC	
Protection class		II	
Max. current load total	[A]	4	
Outputs			
Electrical design		PNP	
Operating conditions			
Ambient temperature	[°C]	-25...90	
Ambient temperature (moving)	[°C]	-25...90	
Protection		IP 65; IP 67; IP 68; IP 69K	
Mechanical data			
Weight	[g]	85.8	
Dimensions	[mm]	15.5 x 15.5 x 45	
Moulded-body material		TPU	
Material nut		brass, anti-spatter	
Sealing material		FKM	
Drag chain suitability		yes	
Drag chain suitability		bending radius for flexible use	min. 10 x cable diameter
		travel speed	max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s²
		bending cycles	> 2 Mio.
		torsional strain	± 180 °/m
Displays / operating elements			
Display		switching status	4 x LED, yellow
		operation	2 x LED, green
Remarks			
Pack quantity		1 pcs.	

EVW167

Connecting cable with socket


ADOGH046SCS0002T04

Electrical connection


Cable: 2 m, PUR, Halogen-free, grey, Ø 4.9 mm; not irradiated (can be recycled); resistant to welding sparks; 4 x 0.34 mm² (42 x Ø 0.1 mm)

Electrical connection - socket

Connector: 1 x M12, straight; coding: A; Contacts: 4, gold-plated; Moulded body: TPU, black transparent; Locking: brass, anti-spatter; Sealing: FKM; Tightening torque: 0.6...1.5 Nm



Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue
WH =	white