
# PN7293

## Pressure sensor with display

PN-025-REN14-QFRKG/US/ /V




1 alphanumeric display 4-digit red/green
2 LEDs Display unit / switching status
3 programming button
4 upper part of the housing can be rotated 345°

| | | | |
|---|---|---|---|
| **Product characteristics** | | | |
| Number of inputs and outputs | Number of digital outputs: 2 | | |
| Measuring range | 0...25 bar | 0...362 psi | 0...2.5 MPa |
| Process connection | threaded connection 1/4" NPT internal thread | | |
| **Application** | | | |
| Special feature | Gold-plated contacts | | |
| Measuring element | ceramic-capacitive pressure measuring cell | | |
| Application | for industrial applications | | |
| Media | liquids and gases | | |
| Medium temperature [°C] | -25...80 | | |
| Min. burst pressure | 350 bar | 5075 psi | 35 MPa |
| Pressure rating | 150 bar | 2175 psi | 15 MPa |
| Type of pressure | relative pressure | | |
| MAWP for applications according to CRN | 70 bar | 1015 psi | 7 MPa |
| **Electrical data** | | | |
| Operating voltage [V] | 18...30 DC; (to SELV/PELV) | | |
| Current consumption [mA] | < 35 | | |
| Min. insulation resistance [MΩ] | 100; (500 V DC) | | |
| Protection class | III | | |
| Reverse polarity protection | yes | | |

# PN7293

## Pressure sensor with display

PN-025-REN14-QFRKG/US/ /V

| | | | |
|---|---|---|---|
| Power-on delay time [s] | < 0.3 | | |
| Integrated watchdog | yes | | |
| **Inputs / outputs** | | | |
| Number of inputs and outputs | Number of digital outputs: 2 | | |
| **Outputs** | | | |
| Total number of outputs | 2 | | |
| Output signal | switching signal; IO-Link; (configurable) | | |
| Electrical design | PNP/NPN | | |
| Number of digital outputs | 2 | | |
| Output function | normally open / normally closed; (parameterisable) | | |
| Max. voltage drop switching output DC [V] | 2.5 | | |
| Permanent current rating of switching output DC [mA] | 150; (200 (...60 °C) 250 (...40 °C)) | | |
| Switching frequency DC [Hz] | < 170 | | |
| Short-circuit protection | yes | | |
| Type of short-circuit protection | pulsed | | |
| Overload protection | yes | | |
| **Measuring/setting range** | | | |
| Measuring range | 0...25 bar | 0...362 psi | 0...2.5 MPa |
| Factory setting / CMPT = 2 | | | |
| Set point SP | 0.2...25 bar | 4...362 psi | 0.02...2.5 MPa |
| Reset point rP | 0.1...24.9 bar | 2...360 psi | 0.01...2.49 MPa |
| Min. difference between SP and rP | 0.2 bar | 2 psi | 0.02 MPa |
| In steps of | 0.1 bar | 2 psi | 0.01 MPa |
| Status_B High Resolution / CMPT = 3 | | | |
| Set point SP | 0.2...25 bar | 3...363 psi | 0.02...2.5 MPa |
| Reset point rP | 0.1...24.9 bar | 1...361 psi | 0.01...2.49 MPa |
| Min. difference between SP and rP | 0.2 bar | 2 psi | 0.02 MPa |
| In steps of | 0.1 bar | 1 psi | 0.01 MPa |
| **Accuracy / deviations** | | | |
| Switch point accuracy [% of the span] | < ± 0,5 | | |
| Repeatability [% of the span] | < ± 0,1; (with temperature fluctuations < 10 K) | | |
| Characteristics deviation [% of the span] | < ± 0,25 (BFSL) / < ± 0,5 (LS); (BFSL = Best Fit Straight Line; LS = limit value setting) | | |
| Hysteresis deviation [% of the span] | < ± 0,25 | | |
| Long-term stability [% of the span] | < ± 0,05; (per 6 months) | | |
| Temperature coefficient zero point [% of the span / 10 K] | < ± 0,2; (-0...80 °C) | | |
| Temperature coefficient span | < ± 0,2; (-0...80 °C) | | |

# PN7293

## Pressure sensor with display

PN-025-REN14-QFRKG/US/ /V

| | | | |
|---|---|---|---|
| [% of the span / 10 K] | | | |
| **Response times** | | | |
| Response time | [ms] | < 3 | |
| Delay time programmable dS, dr | [s] | 0...50 | |
| **Software / programming** | | | |
| Parameter setting options | | hysteresis / window; normally open / normally closed; switching logic; switch-on/switch-off delay; Damping; Display unit | |
| **Interfaces** | | | |
| Communication interface | | IO-Link | |
| Transmission type | | COM2 (38,4 kBaud) | |
| IO-Link revision | | 1.1 | |
| SDCI standard | | IEC 61131-9 | |
| SIO mode | | yes | |
| Required master port type | | A; (when pin 2 not connected: B) | |
| Supported DeviceIDs | | **Type of operation** | **DeviceID** |
| | | Factory setting / CMPT = 2 | 453 |
| | | Status_B High Resolution / CMPT = 3 | 631 |
| Note | | For further information please see the IODD PDF file under "Downloads" | |
| Factory setting / CMPT = 2 | | | |
| Profiles | | Smart Sensor - SSP 0 | Generic Profiled Sensor |
| | | Function | Device identification |
| | | Function | Process data variable |
| | | Function | Device diagnosis |
| Min. process cycle time | [ms] | 2.3 | |
| IO-Link resolution pressure | | 0.1 bar | 0.01 MPa |
| IO-Link process data (cyclical) | | **function** | **bit length** |
| | | pressure | 14 |
| | | binary switching information | 2 |
| IO-Link functions (acyclical) | | application specific tag | |
| Status_B High Resolution / CMPT = 3 | | | |
| Profiles | | Smart Sensor - SSP 3.1 | Measuring Sensor |
| | | Common - I&D | Identification and Diagnosis |
| Min. process cycle time | [ms] | 3 | |
| IO-Link resolution pressure | | 0.01 bar | 0.001 MPa |
| IO-Link process data (cyclical) | | **function** | **bit length** |
| | | pressure | 16 |
| | | device status | 4 |
| | | binary switching information | 2 |
| IO-Link functions (acyclical) | | application specific tag | |
| **Operating conditions** | | | |
| Ambient temperature | [°C] | -25...80 | |
| Storage temperature | [°C] | -40...100 | |
| Protection | | IP 65; IP 67 | |

# PN7293

## Pressure sensor with display

PN-025-REN14-QFRKG/US/ /V

| Tests / approvals | | | |
|---|---|---|---|
| EMC | | DIN EN 61000-6-2 | |
| | | DIN EN 61000-6-3 | |
| Shock resistance | | DIN EN 60068-2-27 | 50 g (11 ms) |
| Vibration resistance | | DIN EN 60068-2-6 | 20 g (10...2000 Hz) |
| MTTF | [years] | 260 | |
| UL approval | | UL approval no. | J001 |
| Pressure Equipment Directive | | Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request | |

| Mechanical data | | |
|---|---|---|
| Weight | [g] | 223.5 |
| Housing | | cylindrical |
| Dimensions | [mm] | Ø 34 / L = 90.7 |
| Materials | | stainless steel (316L/1.4404); PBT+PC-GF30; PBT-GF20; PC |
| Materials (wetted parts) | | stainless steel (316L/1.4404); ceramics; FKM |
| Min. pressure cycles | | 100 million |
| Tightening torque | [Nm] | 2...3 turns after hand-fastening; recommended tightening torque; depends on the lubrication, the seal and the pressure load |
| Process connection | | threaded connection 1/4" NPT internal thread |
| Restrictor element integrated | | no (can be retrofitted) |

| Displays / operating elements | | |
|---|---|---|
| Display | Display unit | 3 x LED, green (bar, psi, MPa) |
| | switching status | 2 x LED, yellow |
| | measured values | alphanumeric display, red/green 4-digit |

| Remarks | |
|---|---|
| Pack quantity | 1 pcs. |

## Electrical connection

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated




# PN7293

## Pressure sensor with display

PN-025-REN14-QFRKG/US/ /V

### Connection




| | |
|---|---|
| OUT1 | switching output<br>IO-Link |
| OUT2 | switching output |
| | colours to DIN EN 60947-5-2 |
| | Core colours : |
| BK = | black |
| BN = | brown |
| BU = | blue |
| WH = | white |