
# EVW030

## Connection cable

VDOAH040SCS0001T04STGH040SCS




| | | |
|---|---|---|
| **Application** | | |
| Special feature | | Free from silicone; Halogen-free; Gold-plated contacts; Drag chain suitability |
| Application | | welding applications |
| Free from silicone | | yes |
| **Electrical data** | | |
| Operating voltage | [V] | < 250 AC / < 300 DC |
| Protection class | | II |
| Max. current load total | [A] | 4 |
| **Operating conditions** | | |
| Ambient temperature | [°C] | -25...90 |
| Note on ambient temperature | | cULus: ...75 |
| Ambient temperature (moving) | [°C] | -25...90 |
| Note on ambient temperature (moving) | | cULus: ...75 |
| Storage temperature | [°C] | -25...55 |
| Storage humidity | [%] | 10...100 |
| Other climatic conditions for storage according to stated class | | 1K22/ DIN 60721-3-1 |
| Protection | | IP 65; IP 67; IP 68; IP 69K |
| **Mechanical data** | | |
| Weight | [g] | 68.3 |
| Moulded-body material | | TPU |
| Material nut | | brass, anti-spatter |
| Sealing material | | FKM |
| Drag chain suitability | | yes |
| Drag chain suitability | | bending radius for flexible use: min. 10 x cable diameter |
| | | travel speed: max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s² |
| | | bending cycles: > 2 Mio. |
| | | torsional strain: ± 180 °/m |
| **Remarks** | | |
| Remarks | | with 2 label holders 30 mm long |

# EVW030

## Connection cable

VDOAH040SCS0001T04STGH040SCS

| | |
|---|---|
| Pack quantity | 1 pcs. |

### Electrical connection - plug


Connector: 1 x M12, straight; coding: A; Contacts: 4, gold-plated; Moulded body: TPU, orange; Locking: brass, anti-spatter; Tightening torque: 0.6...1.5 Nm




### Electrical connection


Cable: 1 m, PUR, Halogen-free, grey, Ø 4.9 mm; not irradiated (can be recycled); resistant to welding sparks; 4 x 0.34 mm² (42 x Ø 0.1 mm )

Connection





### Electrical connection - socket

Connector: 1 x M12, angled; coding: A; Contacts: 4, gold-plated; Moulded body: TPU, orange; Locking: brass, anti-spatter; Sealing: FKM; Tightening torque: 0.6...1.5 Nm




### Diagrams and graphs

characteristic line for derating




Derating Imax * 0.8 (DIN EN 60512-5-2)

X Ambient temperature [°C]

Y Current [A]