
# IIC207

## Inductive sensor

IIK3022-BPKG/US-104

phase-out article
Discontinuation date: 03/31/2026

Alternative articles: IIS227
When selecting an alternative article and accessories please note that technical data may differ!




| | | |
|---|---|---|
| **Product characteristics** | | |
| Electrical design | | PNP |
| Output function | | normally open |
| Sensing range | [mm] | 22 |
| Housing | | threaded type |
| Dimensions | [mm] | M30 x 1.5 / L = 60 |
| **Application** | | |
| Special feature | | Gold-plated contacts |
| Application | | Industrial applications / factory automation; Use in machine tools, coolants and lubricants |
| **Electrical data** | | |
| Operating voltage | [V] | 10...30 DC |
| Current consumption | [mA] | 10 |
| Protection class | | II |
| Reverse polarity protection | | yes |
| **Outputs** | | |
| Electrical design | | PNP |
| Output function | | normally open |
| Max. voltage drop switching output DC | [V] | 2.5 |
| Permanent current rating of switching output DC | [mA] | 200 |
| Switching frequency DC | [Hz] | 100 |
| Short-circuit protection | | yes |
| Type of short-circuit protection | | pulsed |
| Overload protection | | yes |

# IIC207


## Inductive sensor

IIK3022-BPKG/US-104

| | | | |
|---|---|---|---|
| **Detection zone** | | | |
| Sensing range | [mm] | 22 | |
| Real sensing range Sr | [mm] | 22 ± 10 % | |
| Operating distance | [mm] | 0...17.82 | |
| **Accuracy / deviations** | | | |
| Correction factor | | steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3 | |
| Hysteresis | [% of Sr] | 1...20 | |
| Switch point drift | [% of Sr] | -10...10 | |
| **Operating conditions** | | | |
| Ambient temperature | [°C] | -25...70 | |
| Protection | | IP 68 | |
| **Tests / approvals** | | | |
| EMC | | EN 61000-4-2 ESD | 4 kV CD / 8 kV AD |
| | | EN 61000-4-3 HF radiated | 10 V/m |
| | | EN 61000-4-4 Burst | 2 kV |
| | | EN 61000-4-6 HF conducted | 10 V |
| | | EN 55011 | class B |
| MTTF | [years] | 1083 | |
| UL approval | | Ta | 0...40 °C |
| | | Enclosure type | Type 1 |
| | | voltage supply | Limited Voltage/Current |
| | | UL approval no. | A043 |
| | | File number UL | E174191 |
| **Mechanical data** | | | |
| Weight | [g] | 113.8 | |
| Housing | | threaded type | |
| Mounting | | non-flush mountable | |
| Dimensions | [mm] | M30 x 1.5 / L = 60 | |
| Thread designation | | M30 x 1.5 | |
| Materials | | housing: brass white bronze coated; sensing face: LCP white; LED window: PEI; lock nuts: brass white bronze coated | |
| Tightening torque | [Nm] | 50 | |
| **Displays / operating elements** | | | |
| Display | | switching status | 4 x LED, yellow |
| **Accessories** | | | |
| Items supplied | | lock nuts: 2 | |
| **Remarks** | | | |
| Pack quantity | | 1 pcs. | |

**Electrical connection - plug**

Connector: 1 x M12; coding: A; Contacts: 3, gold-plated



# IIC207

## Inductive sensor

**IIK3022-BPKG/US-104**

## Connection

