
SF311A

Flow sensor for connection to an evaluation unit

SFR12ADB/1/2G /6M



Product characteristics			
Probe length L	[mm]	12	
Process connection		threaded connection G 1/2 external thread	
Application			
Media		Liquids; Gases	
Medium temperature	[°C]	-20...60	
Pressure rating		300 bar	30 MPa
Liquids			
Medium temperature	[°C]	-20...60	
Gases			
Medium temperature	[°C]	-20...60	
Electrical data			
Connection to control monitor		VS2000 Exi (PTB 01 ATEX 2075)	
Measuring/setting range			
Probe length L	[mm]	12	
Liquids			
Setting range	[cm/s]	3...300	
Greatest sensitivity	[cm/s]	3...60	
Gases			
Setting range	[cm/s]	200...2000	
Greatest sensitivity	[cm/s]	200...800	
Accuracy / deviations			
Temperature gradient	[K/min]	15	
Response times			
Response time	[s]	1...10	
Liquids			
Response time	[s]	1...10	
Gases			
Response time	[s]	1...10	
Operating conditions			
Ambient temperature	[°C]	-20...60	

SF311A

Flow sensor for connection to an evaluation unit

SFR12ADB/1/2G /6M

Storage temperature	[°C]	-20...85	
Protection		IP 67	
Tests / approvals			
Approval		DMT 03 ATEX E 090 X; TIIS TC17434; IECEx BVS 11.0017 X	
ATEX marking		II 1/2G Ex ia IIC T4 Ga/Gb	
Shock resistance		DIN IEC 68-2-27	40 g (11 ms)
Vibration resistance		DIN IEC 68-2-6	10 g (55...2000 Hz)
MTTF	[years]	8648	
Safety classification			
Max. internal capacitance	[nF]	1.2	
Max. internal inductance	[µH]	6	
Temperature class		T4	
Mechanical data			
Weight	[g]	467	
Housing		cylindrical	
Materials		stainless steel (316L/1.4404)	
Materials (wetted parts)		stainless steel (316L/1.4404)	
Process connection		threaded connection G 1/2 external thread	
Probe diameter	[mm]	8.2	
Installation length EL	[mm]	45	
Remarks			
Remarks		In principle, the type test according to 94/9/EC (ATEX) only takes atmospheric conditions into account (0.8...1.1 bar).	
		For pressures outside this range use must be assessed and approved by the user.	
		Adhere to the operating instructions and the type test certificate.	
Pack quantity		1 pcs.	

SF311A


Flow sensor for connection to an evaluation unit

SFR12ADB/1/2G /6M

Electrical connection

Cable: 6 m, TPE-S; Maximum cable length: 100 m; 5 x 0.34 mm²

Connection



	Core colours :
BN =	brown
BU =	blue
BK =	black
WH =	white
GY =	grey