
PG2452

Pressure sensor with analogue display

PG-100-REB12-MFRKG/US/ /P

phase-out article

Alternative articles: PG1402
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics			
Number of inputs and outputs	Number of digital outputs: 1; Number of analogue outputs: 1		
Measuring range	0...100 bar	0...1449 psi	
Process connection	threaded connection G 1/2 external thread		
Application			
Special feature	Gold-plated contacts		
Application	for industrial applications		
Media	liquids and gases		
Conditionally suitable for	use in gases at pressures > 25 bar only on request		
Medium temperature [°C]	-25...80		
Min. burst pressure	700 bar	9400 psi	70 MPa
Pressure rating	300 bar	4350 psi	30 MPa
Type of pressure	relative pressure		

PG2452

Pressure sensor with analogue display

PG-100-REB12-MFRKG/US/ /P

Electrical data			
Operating voltage	[V]	18...32 DC	
Current consumption	[mA]	< 70; (24 V)	
Min. insulation resistance	[MΩ]	100; (500 V DC)	
Protection class		III	
Reverse polarity protection		yes	
Power-on delay time	[s]	6	
Integrated watchdog		yes	
Inputs / outputs			
Number of inputs and outputs		Number of digital outputs: 1; Number of analogue outputs: 1	
Outputs			
Total number of outputs		2	
Output signal		switching signal; analogue signal; (configurable)	
Electrical design		PNP/NPN	
Number of digital outputs		1	
Output function		normally open / normally closed; (parameterisable)	
Max. voltage drop switching output DC	[V]	2	
Permanent current rating of switching output DC	[mA]	250	
Switching frequency DC	[Hz]	75	
Number of analogue outputs		1	
Analogue current output	[mA]	4...20, invertible; (scalable)	
Max. load	[Ω]	(Ub - 10 V) / 20 mA	
Short-circuit protection		yes	
Type of short-circuit protection		pulsed	
Overload protection		yes	
Measuring/setting range			
Measuring range		0...100 bar	0...1449 psi
Set point SP		0.4...160 bar	6...2322 psi
Reset point rP		0...159.6 bar	0...2316 psi
Analogue start point		0...135 bar	0...1959 psi
Analogue end point		25...160 bar	363...2322 psi
In steps of		0.2 bar	3 psi
Accuracy / deviations			
Switch point accuracy	[% of the span]	< ± 0,5; (Turn down 1:1)	
Repeatability	[% of the span]	< ± 0,1; (with temperature fluctuations < 10 K; Turn down 1:1)	
Characteristics deviation	[% of the span]	< ± 0,25 (BFSL) / < ± 0,5 (LS); (Turn down 1:1; BFSL = Best Fit Straight Line)	
Hysteresis deviation	[% of the span]	< ± 0,25; (Turn down 1:1)	
Long-term stability	[% of the span]	< ± 0,1; (Turn down 1:1; per 6 months)	

PG2452

Pressure sensor with analogue display

PG-100-REB12-MFRKG/US/ /P

Temperature coefficient zero point [% of the span / 10 K]		< ± 0,2; (0...70 °C)	
Temperature coefficient span [% of the span / 10 K]		< ± 0,2; (0...70 °C)	
Response times			
Response time	[ms]	< 9	
Damping process value dAP	[s]	0.01...30	
Damping for the analogue output dAA	[s]	0.01...30	
Step response time analogue output	[ms]	28	
Operating conditions			
Ambient temperature	[°C]	-20...80	
Storage temperature	[°C]	-40...100	
Protection		IP 67; IP 69K	
Tests / approvals			
EMC		EN 61000-4-2 ESD	4 kV CD / 8 kV AD
		EN 61000-4-3 HF radiated	10 V/m
		EN 61000-4-4 Burst	2 kV
		EN 61000-4-5 Surge	0,5/1 kV
		EN 61000-4-6 HF conducted	10 V
Shock resistance		DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance		DIN EN 60068-2-6	10 g (10...2000 Hz)
MTTF	[years]	100	
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data			
Weight	[g]	564.2	
Dimensions	[mm]	169 x 100 x 57	
Materials		stainless steel (316L/1.4404); PA; FKM; PTFE; viewing glass: laminated safety glass 4 mm	
Materials (wetted parts)		Al2O3 (ceramics); FKM; stainless steel (316L/1.4404)	
Min. pressure cycles		100 million	
Process connection		threaded connection G 1/2 external thread	
Restrictor element integrated		no (can be retrofitted)	
Displays / operating elements			
Display		Display unit	2 x LED, green
		switching status	LED, yellow
		switch points	LED ring, red
		function display	alphanumeric display, red 4-digit
		measured values	analogue display, 0...350° rotatable, pointer not visible when unit disconnected
		measured values	alphanumeric display, red 4-digit
With scale		yes	
Extended display range (max.)		160 bar	2322 psi
Remarks			
Remarks		switch point accuracy in the extended display range: 1.5 % of the span	

PG2452

Pressure sensor with analogue display

PG-100-REB12-MFRKG/US/ /P


Pack quantity	1 pcs.


Electrical connection

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



Connection





OUT1	switching output
OUT2	analogue output