




Inductive high-temperature sensor

IGA3008ZBPKG/5M/SH



Product characteristics		
Electrical design		PNP
Output function		normally open
Sensing range	[mm]	8
Housing		threaded type
Dimensions	[mm]	M18 x 1 / L = 77
Application		
Application		high-temperature applications
Electrical data		
Operating voltage	[V]	10...35 DC
Current consumption	[mA]	< 15
Protection class		III
Reverse polarity protection		yes
Outputs		
Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	150
Switching frequency DC	[Hz]	400
Short-circuit proof		yes
Overload protection		yes
Detection zone		
Sensing range	[mm]	8
Operating distance	[mm]	0...6.5
Accuracy / deviations		
Correction factor		stainless steel: 0.6 / brass: 0.3 / aluminium: 0.2 / copper: 0.1
Hysteresis	[% of Sr]	3...15
Switch point drift	[% of Sr]	-15...15
Operating conditions		
Ambient temperature	[°C]	0...180
Protection		IP 65

IG6119



Inductive high-temperature sensor

IGA3008ZBPKG/5M/SH

Tests / approvals		
EMC	EN 61000-4-2 ESD	2 kV CD / 4 kV AD
	EN 61000-4-3 HF radiated	3 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	3 V
MTTF	[years]	683


Mechanical data		
Weight	[g]	262.5
Housing		threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M18 x 1 / L = 77
Thread designation		M18 x 1
Materials		threaded sleeve: stainless steel; sensing face: LCP

Accessories	
Items supplied	lock nuts: 2

Remarks	
Pack quantity	1 pcs.

Electrical connection	
Cable: 5 m, silicone; highly flexible; 3 x 0.22 mm²	

Connection	
------------	--



	Core colours :
BK =	black
BN =	brown
BU =	blue