


IS5035



Inductive sensor

IS-3002-BPKG/AS



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	2
Housing	rectangular
Dimensions [mm]	36.8 x 10.2 x 16

Application

Application	Industrial applications; For use where space is restricted
-------------	--

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	15
Protection class	III
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	800
Short-circuit protection	yes
Overload protection	yes

Monitoring range

Sensing range [mm]	2
Real sensing range Sr [mm]	2 ± 10 %

IS5035



Inductive sensor

IS-3002-BPKG/AS

Operating distance	[mm]	0...1.6
--------------------	------	---------

Accuracy / deviations

Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 65; (with ifm socket duly screwed on: IP 67)

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[years]	3060
UL approval	Ta	-25...80 °C
	Enclosure type	Type 1
	voltage supply	Class 2
	File number UL	E174191

Mechanical data

Weight	[g]	10.9
Housing		rectangular
Mounting		flush mountable
Dimensions	[mm]	36.8 x 10.2 x 16
Material		housing: PBT
Tightening torque	[Nm]	< 0.5; (with washer)

Displays / operating elements

Display	Switching status	4 x 90° LED, yellow
---------	------------------	---------------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M8; coding: A; Contacts: 3



IS5035



Inductive sensor

IS-3002-BPKG/AS

Connection

