
# MS5010

## Magnetic sensor

MS-3060-BPKG/AS-510-TPS




| | | |
|---|---|---|
| **Product characteristics** | | |
| Electrical design | | PNP |
| Output function | | normally open |
| Sensing range | [mm] | 60;  (referred to magnet M 4.0) |
| Housing | | rectangular |
| Dimensions | [mm] | 36.8 x 10.2 x 16 |
| **Application** | | |
| Special feature | | Gold-plated contacts |
| **Electrical data** | | |
| Operating voltage | [V] | 10...30 DC;  ("supply class 2" to cULus) |
| Current consumption | [mA] | < 10 |
| Protection class | | III |
| Reverse polarity protection | | yes |
| **Outputs** | | |
| Electrical design | | PNP |
| Output function | | normally open |
| Max. voltage drop switching output DC | [V] | 2.5 |
| Permanent current rating of switching output DC | [mA] | 200 |
| Switching frequency DC | [Hz] | 5000 |
| Short-circuit protection | | yes |
| Type of short-circuit protection | | pulsed |
| Overload protection | | yes |
| **Detection zone** | | |
| Sensing range | [mm] | 60;  (referred to magnet M 4.0) |

# MS5010

## Magnetic sensor

MS-3060-BPKG/AS-510-TPS

| | | | |
|---|---|---|---|
| Response sensitivity | [mT] | 1.2 | |
| **Accuracy / deviations** | | | |
| Hysteresis | [% of Sr] | 1...10 | |
| **Operating conditions** | | | |
| Ambient temperature | [°C] | -25...75 | |
| Protection | | IP 67 | |
| **Tests / approvals** | | | |
| EMC | | EN 61000-4-2 ESD | 4 kV CD / 8 kV AD |
| | | EN 61000-4-3 HF radiated | 10 V/m |
| | | EN 61000-4-4 Burst | 2 kV |
| | | EN 61000-4-5 Surge | 0,5 kV line to line, Ri: 2 Ohm |
| | | EN 61000-4-6 HF conducted | 10 V |
| | | EN 55011 | class B |
| MTTF | [years] | 2847 | |
| **Mechanical data** | | | |
| Weight | [g] | 17 | |
| Housing | | rectangular | |
| Dimensions | [mm] | 36.8 x 10.2 x 16 | |
| Materials | | housing: PBT orange | |
| **Displays / operating elements** | | | |
| Display | | switching status | 1 x LED, yellow |
| **Remarks** | | | |
| Pack quantity | | 1 pcs. | |
| **Electrical connection - plug** | | | |

Connector: 1 x M8; coding: A; Contacts: 3, gold-plated




Connection

