
MFS210

Full-metal magnetic sensor

MFK3060-APKG/AM/G/US



Product characteristics			
Electrical design		PNP	
Output function		normally closed	
Sensing range	[mm]	60; (referred to magnet M 4.0)	
Housing		threaded type	
Dimensions	[mm]	M12 x 1 / L = 60	
Application			
Special feature		Gold-plated contacts; Full-metal housing	
Pressure rating		100 bar	10 MPa
Electrical data			
Operating voltage	[V]	10...30 DC	
Current consumption	[mA]	< 10	
Protection class		III	
Reverse polarity protection		yes	
Outputs			
Electrical design		PNP	
Output function		normally closed	
Max. voltage drop switching output DC	[V]	2.5	
Permanent current rating of switching output DC	[mA]	200	
Switching frequency DC	[Hz]	5000	
Short-circuit protection		yes	
Overload protection		yes	
Detection zone			
Sensing range	[mm]	60; (referred to magnet M 4.0)	
Response sensitivity	[mT]	1.3	
Accuracy / deviations			
Hysteresis	[% of Sr]	1...10	
Operating conditions			
Ambient temperature	[°C]	-25...75	
Protection		IP 65; IP 67	

MFS210

Full-metal magnetic sensor

MFK3060-APKG/AM/G/US

Tests / approvals			
EMC		EN 61000-4-2 ESD	4 kV CD / 8 kV AD
		EN 61000-4-3 HF radiated	10 V/m
		EN 61000-4-4 Burst	2 kV
		EN 61000-4-5 Surge	0,5 kV line to line, Ri: 2 Ohm
		EN 61000-4-6 HF conducted	10 V
		EN 55011 emission	class B
		DIN ISO 11452-2	100 V/m
MTTF	[years]	1370	
Mechanical data			
Weight	[g]	27.8	
Housing		threaded type	
Dimensions	[mm]	M12 x 1 / L = 60	
Thread designation		M12 x 1	
Materials		housing: stainless steel (316L/1.4404); sensing face: stainless steel (316L/1.4404); LED window: PA; lock nuts: brass	
Full-metal housing		yes	
Displays / operating elements			
Display		switching status	4 x 90° LED, yellow
Accessories			
Items supplied		lock nuts: 2	
Remarks			
Pack quantity		1 pcs.	

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



Connection

