
E80384

RFID tag

ID-TAG/D50x3,0/0 2528 bit



Application		
Operating temperature (active)	[°C]	-40...85
Peak temperature (passive)	[°C]	90
Electrical data		
Operating frequency	[MHz]	13,56
Memory size	[bit]	1024
Memory type		EEPROM
Chip type		ICODE SLIX
Number of blocks		28
Block size	[Byte]	4
Unique Identification Number (UID)	[Byte]	8
RFID standard		ISO 15693
Max. read cycles		unlimited
Max. write cycles		100000
Operating conditions		
Ambient temperature	[°C]	-40...85
Storage temperature	[°C]	-40...90
Protection		IP 68; IP 69K
Tests / approvals		
Shock resistance	DIN IEC 68-2-27	40 g 18 ms
Vibration resistance	DIN IEC 68-2-6	10 g 10...2000 Hz
Radio approval		ISO 15693
Mechanical data		
Weight	[g]	11.55
Type of mounting		installation on non-metal materials; (screw fastening ; sticking to a surface)
Dimensions	[mm]	Ø 50 / L = 3
Materials		PPA black
Remarks		
Pack quantity		1 pcs.

E80384

RFID tag

ID-TAG/D50x3,0/0 2528 bit

Other data	
Reading distance when mounted on non-metal (mm)	
ANT410 / DTI110 / DTI410	15
ANT411 / DTI111 / DTI411	25
ANT420 / DTI120 / DTI420 / DTI424 / DTI124 / DTM424 / DTM426	15
ANT421 / DTI121 / DTI421 / DTI125 / DTI425 / DTM425 / DTM427	50
ANT430 / DTI130 / DTI430 / DTI134 / DTI434 / DTM434 / DTM436	35
ANT431 / DTI131 / DTI431 / DTI135 / DTI435 / DTM435 / DTM437	65
ANT513 / DTI213 / DTI513 / DTC510	90
ANT515 / DTI215 / DTI515 / ANT516 / DTI516	50
ANT600 / DTI600	190