




Retro-reflective sensor

OUR-DPKG/US-100-DPS



Product characteristics

Type of light	infrared light
Housing	rectangular

Application

Function principle	Retro-reflective sensor
Application	Industrial applications / factory automation

Electrical data

Operating voltage	[V]	10...55 DC; ("supply class 2" to cULus)
Current consumption	[mA]	35; ((24 V))
Protection class		III
Reverse polarity protection		yes
Type of light		infrared light
Wave length	[nm]	880

Outputs

Electrical design		PNP
Output function		dark-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	160
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Range referred to prismatic reflector	[m]	0.15...3; (Prismatic reflector Ø 80 E20005)
Range adjustable		yes
Max. light spot diameter	[mm]	262
Light spot dimensions refer to		at maximum range



Retro-reflective sensor

OUR-DPKG/US-100-DPS

Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2	
MTTF	[years]	694
UL approval	Ta	< 40 °C
	Enclosure type	Type 1
	voltage supply	Class 2
	UL approval no.	E032
	File number UL	E174191
Mechanical data		
Weight	[g]	75
Housing		rectangular
Dimensions	[mm]	28 x 16 x 51
Number of channels		1
Materials		housing: PPO modified
Lens material		front pane:glass
Displays / operating elements		
Display	switching status	1 x LED, yellow
Accessories		
Items supplied		Angle bracket: 1, E20211
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Connector: 1 x M12; coding: A; Contacts: 4		
Connection		



Retro-reflective sensor

OUR-DPKG/US-100-DPS

Diagrams and graphs

excess gain graph

