


E80426



RFID tag

ID-TAG/D30x2.5/6 - 896 bit



Application

Operating temperature (active)	[°C]	-40...85
Peak temperature (passive)	[°C]	90

Electrical data

Operating frequency	[MHz]	13,56
Memory size	[bit]	896
Memory type		EEPROM
Chip type		ICODE SLIX
Number of the blocks		28
Block size	[Byte]	4
Unique Identification Number (UID)	[Byte]	8
RFID standard		ISO 15693
Max. read cycles		unlimited
Max. write cycles		100000

Operating conditions

Ambient temperature	[°C]	-40...85
Storage temperature	[°C]	-40...90
Protection		IP 68; IP 69K

Tests / approvals

Shock resistance	DIN IEC 68-2-27	40 g 18 ms
Vibration resistance	DIN IEC 68-2-6	10 g 10...2000 Hz
Radio approval		ISO 15693

Mechanical data

Weight	[g]	31
Type of mounting		installation on non-metal materials; (screw fastening ; sticking to a surface)
Dimensions	[mm]	Ø 30 / L = 3
Material		PA 6 black

Remarks

Pack quantity	10 pcs.
---------------	---------

E80426



RFID tag

ID-TAG/D30x2.5/6 - 896 bit

Other data

Reading distance when mounted on non-metal (mm)

ANT410 / DTI110 / DTI410	15
ANT411 / DTI111 / DTI411	20
ANT420 / DTI120 / DTI420 / DTI124 / DTI424 / DTM424 / DTM426	15
ANT421 / DTI121 / DTI421 / DTI125 / DTI425 / DTM425 / DTM427	40
ANT430 / DTI130 / DTI430 / DTI134 / DTI434 / DTM434 / DTM436	30
ANT431 / DTI131 / DTI431 / DTI135 / DTI435 / DTM435 / DTM437	50
ANT513 / DTI213 / DTI513 / DTC510	65
ANT515 / DTI215 / DTI515 / ANT516 / DTI216 / DTI516	35
ANT600 / DTI600	140