


TS2289



Temperature cable sensor with process connection

TS-200KLKD6-...../US/



Product characteristics

Measuring range	-40...90 °C	-40...194 °F
Process connection	Clamp fitting Ø 6 mm	
Installation length EL [mm]	45	

Application

Special feature	gold-plated contacts
Measuring element	1 x Pt 100; (to DIN EN 60751, class A)
Media	liquids and gases
Minimum installation depth [mm]	15

Electrical data

Protection class	III
------------------	-----

Measuring/setting range

Probe length L	[mm]	45	
Measuring range		-40...90 °C	-40...194 °F

Accuracy / deviations

Accuracy [K]	$\pm (0,15 K + 0,002 \times t)$
--------------	-----------------------------------

Reaction times

Dynamic response T05 / T09 [s]	3 / 10; (according to DIN EN 60751)
--------------------------------	-------------------------------------

Operating conditions

Protection	IP 67
------------	-------

Tests / approvals

MTTF [years]	11416
--------------	-------

Mechanical data

Weight [g]	82.2
Housing	tubular
Design	Measuring probes
Dimensions [mm]	Ø 6 / L = 45
Material	stainless steel
Materials (wetted parts)	stainless steel (1.4404 / 316L)
Process connection	Clamp fitting Ø 6 mm
Probe diameter [mm]	6
Installation length EL [mm]	45

TS2289



Temperature cable sensor with process connection

TS-200KDK6-...../US/

Remarks	
Remarks	The values for accuracy apply to flowing water.
Pack quantity	1 pcs.

Electrical connection

Cable: 2 m, PUR

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



Connection

