
AC5227

AS-Interface Airbox with quick mounting technology

AirBox 2x3/2 2DI IP67



Application		
Design		housing for DIN rail mounting
Application		field installation
Medium temperature	[°C]	-10...50
Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Max. current consumption from AS-i	[mA]	180
Integrated watchdog		yes
Inputs / outputs		
Number of inputs and outputs		Number of digital inputs: 2; Number of pneumatic outputs: 2
Inputs		
Number of digital inputs		2
Input circuit of digital inputs		PNP
Sensor supply of the inputs		AS-i
Voltage supply	[V]	20...30; (via flat cable)

AC5227

AS-Interface Airbox with quick mounting technology

AirBox 2x3/2 2DI IP67

Max. total current rating of inputs	[mA]	100				
Input current High	[mA]	6...10				
Input current Low	[mA]	0...2				
Switching level high	[V]	> 11				
Digital inputs protected against short circuits		yes				
Outputs						
Number of pneumatic outputs		2				
Actuator supply outputs		AS-i				
Operating conditions						
Ambient temperature	[°C]	-10...55				
Protection		IP 67				
Tests / approvals						
EMC		EN 50295				
		IEC 61000-6-2				
MTTF	[years]	321				
AS-i classification						
AS-i version		2.11; 3.0				
AS-i addressing		addressing socket				
Extended addressing mode		no				
AS-i master profile		M2; M3; M4				
AS-i profile		S-3.F.F				
AS-i I/O configuration	[hex]	3				
AS-i ID code	[hex]	F.F				
Assignment of the data bits		data bit	D0	D1	D2	D3
		input	1	2	3	4
		socket	I-1	I-2	-	-
		pin	2+4	2+4	-	-
		pneumatic output	-	-	2	4
Mechanical data						
Weight	[g]	355.9				
Housing		rectangular				
Type of mounting		quick mounting; AS-i flat cables directly connectable; mounting on DIN rail; (TH35 (EN 60715))				
Dimensions	[mm]	108 x 85 x 50				
Materials		PA; POM; piercing contacts: CuSn6 nickel-plated and tin-plated				
Pneumatic system		2 x 3/2-way slide valves (free from overlapping)				
Operating pressure range		2...8 bar	0.2...0.8 MPa	29...116 psi		
Air flow at 6/5 bar	[l/min]	500				
Permissible compressed air		non-lubricated compressed air class 6-3-1; lubricated compressed air class 6-3-4				
Manual override		pressing/releasing or pressing/turning/locking				
Tube fittings		8 mm				
Exhaust		exhaust can be discharged through tube connection				

AC5227

AS-Interface Airbox with quick mounting technology

AirBox 2x3/2 2DI IP67

Displays / operating elements

Display	operation	LED, green
	errors	LED, red
	function	LED, yellow

Electrical connection

Module connection	Flat cables

Accessories

Items supplied	lower part
Accessories (optional)	Mounting plate:, E74999
	Module lower part:, E75000
	Protective cap: M12, E73004
	sealing plugs:, E75231
	silencer:, E75232
	Push-in L-fitting:, E75228
	Push-in T-fitting:, E75227


Remarks

Remarks	If not pneumatically operated, E75231 sealing plug must be inserted.
	Avoid ingress of dirt and dust.
	Do not connect any of the following points to an external potential:
	L-, L+, I-1, I-2
	The connections are electrically connected with the AS-i cable.
	Please see the notes on compressed air and EMC/ESD under "Downloads"
Pack quantity	1 pcs.

Electrical connection

quick mounting technology for AS-i flat cable: ; three orientations possible


Connector: M12; coding: A; Contacts: 3



	Inputs
1	voltage supply L+
2	not used
3	Sensor supply L-
4	data input
5	not used

Diagrams and graphs

Pneumatic symbol



2 x 3/2-way slide valves (free from overlapping)