
MK5306

C-slot cylinder sensor

MKC3028-ANKG/G/ZH

phase-out article
Discontinuation date: 03/31/2026

Alternative articles: MK5308
When selecting an alternative article and accessories please note that technical data may differ!



1 fastening clamp
2 Sensing face

Product characteristics		
Electrical design		NPN
Output function		normally open
Dimensions	[mm]	17.5 x 2.8 x 7.7
Application		
Operating principle		GMR-Zelle
Electrical data		
Operating voltage	[V]	10...30 DC; ("supply class 2" to cULus)
Current consumption	[mA]	< 10
Protection class		III
Reverse polarity protection		yes
Max. power-on delay time	[ms]	30
Outputs		
Electrical design		NPN
Output function		normally open
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	10000
Short-circuit protection		yes
Overload protection		yes

MK5306

C-slot cylinder sensor

MKC3028-ANKG/G/ZH

Detection zone			
Response sensitivity	[mT]	2.8	
Travel speed	[m/s]	> 10	
Accuracy / deviations			
Hysteresis	[mm]	1.5	
Repeatability	[mm]	< 0.2	
Operating conditions			
Ambient temperature	[°C]	-25...85	
Protection		IP 65; IP 67	
Tests / approvals			
EMC		EN 61000-4-2 ESD	- CD / 8 kV AD
		EN 61000-4-3 HF radiated	10 V/m
		EN 61000-4-4 Burst	2 kV
		EN 61000-4-6 HF conducted	10 V
		EN 55011	class B
MTTF	[years]	3694	
UL approval		UL approval no.	C008
Mechanical data			
Weight	[g]	18.3	
Mounting		non-flush mountable	
Cylinder type		C-slot cylinders	
Dimensions	[mm]	17.5 x 2.8 x 7.7	
Materials		housing: PA; fastening clamp: stainless steel	
Displays / operating elements			
Display		switching status	1 x LED, yellow
Remarks			
Pack quantity		1 pcs.	

MK5306


C-slot cylinder sensor

MKC3028-ANKG/G/ZH

Electrical connection

Cable: 2 m, PUR; 3 x 0.08 mm²

Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue