
DN4014

Switched-mode power supply 24 V DC

PSU-1AC/24VDC-20A



1 potentiometer 24...28 V DC
2 LED DC ok
3 terminals DC ok Output

Application		
Design		housing for DIN rail mounting
Electrical data		
Frequency AC	[Hz]	47...64
Nominal voltage AC	[V]	< 230
Input voltage range AC	[V]	100...240; (-15 % / +10 %)
Output voltage DC	[V]	24...28
Protection class		I; (IEC 61140)
Overvoltage protection		yes; (< 32 DC)
Output voltage	[V]	adjustable; output voltage to SELV, PELV
Max. output current at min. output voltage	[A]	20
Max. output current at max. output voltage	[A]	17.1
Max. output current peak at min. output voltage	[A]	24
Max. output current peak at max. output voltage	[A]	20.6
Output power (permanent)	[W]	480
Output power (peak)	[W]	576
Note on output power (peak)	[W]	≤ 45 °C permitted continuously; > 45 °C < 1 minute every 10 minutes

DN4014

Switched-mode power supply 24 V DC

PSU-1AC/24VDC-20A

Power factor (nominal voltage 120 V AC / 60 Hz)		0.99
Power factor (nominal voltage 230 V AC / 50 Hz)		0.95
Power reserve	[%]	20
Number of output circuits		1
Max. residual ripple	[mV]	50
Switch-on peak current (nominal voltage 120 V AC / 60 Hz)	[A]	9
Switch-on peak current (nominal voltage 230 V AC / 50 Hz)	[A]	7
Inrush current limitation		yes
Efficiency (nominal voltage 120 V AC / 60 Hz)	[%]	92.7
Efficiency (nominal voltage 230 V AC / 50 Hz)	[%]	94
External input protection		≥ B-10 A / ≥ C-10 A
Derating	[W/K]	12 (60...70 °C)
Mains buffering time (nominal voltage 120 V AC / 60 Hz)	[ms]	26
Mains buffering time (nominal voltage 230 V AC / 50 Hz)	[ms]	26
Input current (nominal voltage 120 V AC / 60 Hz)	[A]	4.36
Input current (nominal voltage 230 V AC / 50 Hz)	[A]	2.33
Power loss (nominal voltage 120 V AC / 60 Hz)	[W]	37.8
Power loss (nominal voltage 230 V AC / 50 Hz)	[W]	30.6
Back feeding protection	[V]	35
Outputs		
Short-circuit proof		yes
Overload protection		yes
Overload performance		Hiccup Mode; In the event of overload / short circuit, the output alternately supplies continuous power for 2 s and then switches off for 18 s.
Type DC-OK signal		relay output
Reliability of the DC OK signal		60 V DC (0.3 A) / 30 V DC (1 A) / 30 V AC (0.5 A)
Operating conditions		
Ambient temperature	[°C]	-25...70
Note on ambient temperature		observe the free space for convection (see operating instructions)
Storage temperature	[°C]	-40...85
Max. relative air humidity	[%]	95; (IEC 60068-2-30)
Protection		IP 20; (EN 60529)
Pollution degree		2; (IEC 62103: conductive soiling not permitted)

DN4014

Switched-mode power supply 24 V DC

PSU-1AC/24VDC-20A

Tests / approvals			
EMC		EN 61000-6-1	
		EN 61000-6-2	
		EN 61000-6-3	
		EN 61000-6-4	
		EN 61000-3-2	Class A
Vibration resistance		IEC 60068-2-6	±1,6 mm 2...17,8 Hz / 2 g 17,8...500 Hz
Shock resistance		IEC 60068-2-27	30 g 6 ms / 20 g 11 ms
MTTF	[years]	53	
Power Factor Correction (PFC)		met	

Mechanical data		
Weight	[g]	1133.35
Housing		rectangular
Type of mounting		mounting on DIN rail; (TH35 (EN 60715))
Dimensions	[mm]	124 x 65 x 132.5
Materials		housing: steel sheet


Displays / operating elements		
Display	DC ok	1 x LED

Remarks	
Remarks	Series connection of outputs only applies to identical units up to max. 150 V DC overall voltage
Pack quantity	1 pcs.

Electrical connection

screw terminals:

Connection



1: primary
2: secondary


DN4014

Switched-mode power supply 24 V DC


PSU-1AC/24VDC-20A


Diagrams and graphs

block diagram



output characteristics





1: output characteristics


2: Hiccup Mode

DN4014


Switched-mode power supply 24 V DC

PSU-1AC/24VDC-20A

characteristic curve for degree of efficiency / power loss



characteristic line for derating



DN4014

Switched-mode power supply 24 V DC

PSU-1AC/24VDC-20A

characteristic line for mains buffering time

