
O6T401

Diffuse reflection sensor

O6T-FNKG/AS/4P



1: output function switch
2: potentiometer sensitivity

Product characteristics		
Type of light		red light
Housing		rectangular
Application		
Function principle		Diffuse reflection sensor
Application		suited for use in the machine tool industry
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	16; ((24 V))
Protection class		III
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	633
Outputs		
Electrical design		NPN
Output function		light-on/dark-on mode; (selectable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	1000
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Detection zone		
Range	[mm]	5...500; (white paper 200 x 200 mm 90% remission)
Setting range	[mm]	100...500

O6T401


Diffuse reflection sensor

O6T-FNKG/AS/4P


Range adjustable			yes
Max. light spot diameter	[mm]		15
Light spot dimensions refer to			at maximum range
Operating conditions			
Ambient temperature	[°C]		-25...60
Protection			IP 65; IP 67; IP 68
Tests / approvals			
EMC		EN 60947-5-2	
MTTF	[years]		910
UL approval		Ta	-25...40 °C
		Enclosure type	Type 1
		voltage supply	Class 2
		UL approval no.	E010
Mechanical data			
Weight	[g]		35.7
Housing			rectangular
Dimensions	[mm]		41.3 x 13 x 21
Materials			housing: stainless steel (316L/1.4404); plastics: PPSU; Sealing: FKM
Lens material			front pane:PMMA
Lens alignment			side lens
Tightening torque	[Nm]		1; (screws)
Displays / operating elements			
Display		switching status	1 x LED, yellow
		operation	1 x LED, green
Remarks			
Remarks			operating voltage "supply class 2" according to cULus
Pack quantity			1 pcs.

Electrical connection

Connector: 1 x M8; coding: A; Contacts: 4



Connection




O6T401

Diffuse reflection sensor

O6T-FNKG/AS/4P

Diagrams and graphs

excess gain graph



x: distance [mm]

y: excess gain factor