


# IN5225



## Dual inductive sensor for valve actuators

IND3004DBPKG/US-100-DPV



Product characteristics	
Electrical design	PNP
Output function	2 x normally open
Sensing range [mm]	4
Housing	rectangular
Dimensions [mm]	40 x 26 x 26
Application	
Special feature	gold-plated contacts
Application	Position sensor for valve actuators
Electrical data	
Operating voltage [V]	10...30 DC
Current consumption [mA]	15
Protection class	II
Reverse polarity protection	yes
Outputs	
Electrical design	PNP
Output function	2 x normally open
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	1300
Short-circuit protection	yes
Type of short-circuit protection	yes (non-latching)
Overload protection	yes
Monitoring range	
Sensing range [mm]	4
Real sensing range Sr [mm]	4 ± 10 %
Operating distance [mm]	0...3.25

# IN5225



## Dual inductive sensor for valve actuators

IND3004DBPKG/US-100-DPV

Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminum: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	1...15
Switch-point drift	[% of Sr]	-10...10

Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67

Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[years]	1064
UL approval	Ta	0...40 °C
	Enclosure type	Type 1
	File number UL	E174191

Mechanical data		
Weight	[g]	40
Housing		rectangular
Mounting		non-flush mountable
Dimensions	[mm]	40 x 26 x 26
Material		housing: PBT
Tightening torque	[Nm]	0.6...1.5; (knurled nut)

Displays / operating elements		
Display	Switching status	2 x LED, yellow

Remarks		
Pack quantity		1 pcs.

### Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated



### Connection

