PNI023


Pressure sensor with analogue input

PNI025-RBR14-QFRKG/US/ V

phase-out article

Alternative articles: DP1204 + PN2093
When selecting an alternative article and accessories please note that technical data may differ!

a DP1204 and two PN2093s are required



1 alphanumeric display 4-digit
2 LEDs Display unit / switching status
3 programming button

Product characteristics			
Number of inputs and outputs		Number of digital outputs: 2	
Measuring range	[bar]	0...25	
Process connection		threaded connection G 1/4 internal thread	
Application			
Special feature		Gold-plated contacts	
Application		for industrial applications	
Media		liquids and gases	
Medium temperature	[°C]	-25...80	
Min. burst pressure		350 bar	35 MPa
Pressure rating		100 bar	10 MPa
Type of pressure		relative pressure	
Electrical data			
Operating voltage	[V]	18...30 DC	
Current consumption	[mA]	< 90	

PNI023

Pressure sensor with analogue input

PNI025-RBR14-QFRKG/US/ V

Min. insulation resistance	[MΩ]	100; (500 V DC)
Protection class		III
Reverse polarity protection		yes
Power-on delay time	[s]	0.2
Integrated watchdog		yes
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 2
Inputs		
Analogue input (current)	[mA]	0...20
Input resistance	[Ω]	300
Analogue input (voltage)	[V]	0...10
Input resistance	[kΩ]	90
Outputs		
Total number of outputs		2
Output signal		switching signal
Electrical design		PNP/NPN
Number of digital outputs		2
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	< 170
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Measuring/setting range		
Measuring range	[bar]	0...25
Set point SP	[bar]	-6.2...25
Note on setpoint SP		differential pressure
Reset point rP	[bar]	-6.3...24.9
Note on reset point rP		differential pressure
In steps of	[bar]	0.1
Accuracy / deviations		
Characteristics deviation [% of the final value]		< ± 0,6
Temperature drift per 10 K		< ± 0.3
Characteristics deviation analogue input		< ± 0.3
Temperature drift analogue input per 10 K		< ± 0.1
Temperature drift analogue input	[°C]	0...80
Response times		
Response time	[ms]	< 3

PNI023

Pressure sensor with analogue input

PNI025-RBR14-QFRKG/US/ V

Delay time programmable dS, dr	[s]	0, 0,1...50
Damping process value dAP	[s]	0...4

Software / programming

Adjustment of the switch point		programming button
Parameter setting options		hysteresis / window; normally open / normally closed; switching logic; current/voltage input; Damping; adaptation of displayed values; display can be rotated and switched off; Display unit

Operating conditions

Ambient temperature	[°C]	-25...80
Storage temperature	[°C]	-40...100
Protection		IP 65

Tests / approvals

EMC		EN 61000-4-2 ESD	4 kV CD / 8 kV AD
		EN 61000-4-3 HF radiated	10 V/m
		EN 61000-4-4 Burst	2 kV
		EN 61000-4-6 HF conducted	10 V
Shock resistance		DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance		DIN IEC 68-2-6	20 g (10...2000 Hz)
MTTF	[years]	152	
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	

Mechanical data

Weight	[g]	289.5
Housing		cylindrical
Dimensions	[mm]	Ø 34 / L = 91.5
Materials		stainless steel (303/1.4305); PBT; PC; PA; FKM
Materials (wetted parts)		stainless steel (303/1.4305); ceramics; FKM
Min. pressure cycles		100 million
Process connection		threaded connection G 1/4 internal thread
Restrictor element integrated		no (can be retrofitted)

Displays / operating elements


Display	Display unit	3 x LED, green
	display mode	3 x LED, green
	switching status	2 x LED, yellow
	function display	alphanumeric display, 4-digit
	measured values	alphanumeric display, 4-digit
Display unit	bar; psi; MPa	

Remarks

Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: 7, gold-plated



PNI023

Pressure sensor with analogue input

PNI025-RBR14-QFRKG/US/ V

Connection

