


SU8651



Ultrasonic flow meter

SUN11XJBFRKG/US



ACS KTW/W270 Reg31

Product characteristics				
Number of inputs and outputs	Number of digital outputs: 2; Number of analog outputs: 1			
Measuring range	1...240 l/min	0.06...14.4 m³/h	16...3804 gph	0.26...63.4 gpm
Nominal diameter	DN25 (1“)			
Process connection	threaded connection 1" NPT external thread DN25			
Application				
Special feature	gold-plated contacts			
Application	use in mobile and industrial applications			
Media	ultra-pure water; water; water-based media; glycol solutions; oils (of high and low viscosity); Coolants			
Note on media	water-based media: for media with >10 % additives, the repeatability is the only available value			
	low-viscosity oils with viscosity: 7...40 mm²/s (40 °C)			
	high-viscosity oils with viscosity: 30...68 mm²/s (40 °C)			
Medium temperature	-40...120 °C		-40...248 °F	
Min. burst pressure	150 bar		15 MPa	
Pressure rating	100 bar		10 MPa	
Vacuum resistance [mbar]	-1000			
Electrical data				
Operating voltage [V]	8...32 DC; (to SELV/PELV)			
Current consumption [mA]	< 175			
Protection class	III			
Reverse polarity protection	yes			

SU8651



Ultrasonic flow meter

SUN11XJBFRKG/US

Power-on delay time	[s]	5			
Measuring principle		ultrasonic			
Inputs / outputs					
Total number of inputs and outputs		2			
Number of inputs and outputs		Number of digital outputs: 2; Number of analog outputs: 1			
Inputs					
Inputs		OUT2	counter reset		
Outputs					
Total number of outputs		2			
Output signal		OUT1	switching signal; pulse signal; diagnostic signal; totalizer switching signal; frequency signal; IO-Link		
		OUT2	switching signal; pulse signal; diagnostic signal; totalizer switching signal; analog signal		
Electrical design		PNP/NPN			
Number of digital outputs		2			
Output function		normally open / closed; (configurable)			
Max. voltage drop switching output DC	[V]	2			
Permanent current rating of switching output DC	[mA]	100			
Switching frequency DC	[Hz]	0...10000			
Number of analog outputs		1			
Analog current output	[mA]	4...20; (scalable)			
Max. load	[Ω]	500			
Analog voltage output	[V]	0...10 / 0.5...4.5; (scalable)			
Min. load resistance	[Ω]	2000			
Pulse output		flow rate meter			
Short-circuit protection		yes			
Type of short-circuit protection		yes (non-latching)			
Overload protection		yes			
Measuring/setting range					
Measuring range		1...240 l/min	0.06...14.4 m³/h	16...3804 gph	0.26...63.4 gpm
Resolution		0.1 l/min	0.001 m³/h	1 gph	0.02 gpm
Note on factory setting		gpm			
		°F			
Set point SP		2.3...240 l/min	0.139...14.4 m³/h	37...3804 gph	0.61...63.4 gpm
Reset point rP		1.1...238.8 l/min	0.064...14.325 m³/h	17...3784 gph	0.28...63.07 gpm
Analog start point ASP		-240...192 l/min	-14.4...11.522 m³/h	-3804...3044 gph	-63.4...50.73 gpm
Analog end point AEP		-191.9...240 l/min	-11.511...14.4 m³/h	-3041...3804 gph	-50.68...63.4 gpm
Low flow cut-off LFC		1...12 l/min	0.06...0.72 m³/h	16...190 gph	0.26...3.17 gpm
Frequency end point, FEP		48.1...240 l/min	2.889...14.4 m³/h	763...3804 gph	12.72...63.4 gpm
Frequency at the end point FRP	[Hz]	1...10000			



Ultrasonic flow meter

SUN11XJBFRKG/US

Volumetric flow quantity monitoring		
Pulse length [s]	0.002...2	
Pulse value	0.1...99990000 l; 0.03...26414563.515 gal	
Temperature monitoring		
Measuring range	-40...120 °C	-40...248 °F
Resolution	0.1 °C	0.1 °F
Set point SP	-40...119.4 °C	-40...247 °F
Reset point rP	-40...88 °C	-40...190.4 °F
Analog start point	-8...120 °C	17.6...248 °F
Analog end point	-40...88 °C	-40...190.4 °F
Frequency start point, FSP	-8...120 °C	17.6...248 °F
Frequency end point, FEP	-40...119.4 °C	-40...247 °F
Frequency at the end point FRP [Hz]	1...10000	
Accuracy / deviations		
Flow monitoring		
Accuracy (in the measuring range)	only up to 100 °C; at higher temperatures, only the repeatability is within the specification.	
Accuracy (in the measuring range)	glycol solutions (35%)	±(5,0 % MW + 0,5 % MEW)
	high-viscosity oils with viscosity 46mm2/s (40°C)	±(5,0 % MW + 0,5 % MEW)
	low-viscosity oils with viscosity 10mm2/s (40°C)	±(5,0 % MW + 0,5 % MEW)
	water	± (1,0 % MW + 0,5 % MEW)
Repeatability	± 0,2 % MEW	
Temperature monitoring		
Accuracy [K]	± 2,5 (Q > 5 % MEW)	
Temperature coefficient [% of the span / 10 K]	0,2	
Reaction times		
Flow monitoring		
Response time [s]	< 0.25; (dAP = 0, T09)	
Damping process value dAP [s]	0...5	
Temperature monitoring		
Dynamic response T05 / T09 [s]	5,7 / 86	
Software / programming		
Diagnostic functions	direction of flow detection; signal quality	
Interfaces		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1.3	
SDCI standard	IEC 61131-9: 2013-07	
Profiles	BLOB	Binary Large Object transfer
	Common - I&D	Identification and Diagnosis
Required master port class	A	
Process data analog	3	

SU8651



Ultrasonic flow meter

SUN11XJBFRKG/US

Process data binary	2	
Min. process cycle time [ms]	9.6	
IO-Link process data (cyclical)	Function	bit length
	totalizer	32
	Flow monitoring	32
	Temperature monitoring	32
	status	4
	Output 1	1
	Output 2	1
Supported DeviceIDs	Type of operation	DeviceID
	default	1828

Operating conditions		
Ambient temperature [°C]		-25...60
Storage temperature [°C]		-40...80
Protection		IP 67; IP 69K

Tests / approvals		
EMC	DIN 61326-1:2021	
Shock resistance	DIN IEC 68-2-27	20 g (11ms)
Vibration resistance	DIN IEC 68-2-6	20 g (10...2000Hz)
MTTF [years]		136
UL approval	UL approval number	I037
	File number UL	E174189
Pressure equipment directive	can be used for group 2 fluids; group 1 fluids on request	

Mechanical data		
Weight [g]		631.5
Housing		rectangular
Inlet pipe length		5 x DN
Outlet pipe length		1 x DN
Dimensions [mm]		162 x 48 x 65.1
Material	housing: stainless steel (1.4404 / 316L); connector: PEI FKM	
Materials (wetted parts)	Pipe section: stainless steel (1.4404 / 316L)	
Nominal diameter		DN25 (1")
Process connection	threaded connection 1" NPT external thread DN25	
Surface characteristics Ra/Rz of the wetted parts		49.21 µin

Displays / operating elements		
Display	operating status	1 x LED, green

Accessories		
Items supplied		package insert

Remarks		
Remarks	MW = Measured value	
	MEW = Final value of the measuring range	
	pulse and totalizer signal are only available for one of the two outputs	
	the accuracy indications are adhered to over the entire application area	
Pack quantity		1 pcs.

SU8651



Ultrasonic flow meter


SUN11XJBFRKG/US

Electrical connection

Connector: 1 x M12; coding: A; Contacts: 4, gold-plated



Connection




1 (L+)	L+	
2 (OUT2)	MP2	DO, AO, Reset
3 (L-)	L-	
4 (OUT1)	MP1	DO, IO-Link

Electrical connection - plug

Diagrams and graphs

Note on pressure loss



dP [psi] Pressure loss
Q [gpm] volumetric flow quantity