


UGT303



Full-metal ultrasonic sensor

UGA401000RRKG/AM/IO/US



Product characteristics

Electrical design	PNP/NPN; (configurable)
Output function	normally open / closed; (configurable)
Sensing range [mm]	100...1000; (Target: 100 x 100 mm)
Communication interface	IO-Link
Housing	Threaded type
Dimensions [mm]	M18 x 1 / L = 98.5

Electrical data

Operating voltage [V]	10...30 DC; (cULus - Class 2 source required)
Current consumption [mA]	< 50
Protection class	III
Reverse polarity protection	yes
Power-on delay time [s]	< 0.5
Converter frequency [kHz]	200

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 2
------------------------------	------------------------------

Outputs

Total number of outputs	2
Electrical design	PNP/NPN; (configurable)
Number of digital outputs	2
Output function	normally open / closed; (configurable)
Max. voltage drop switching output DC [V]	2.2
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	6
Short-circuit protection	yes
Overload protection	yes

Monitoring range

Sensing range [mm]	100...1000; (Target: 100 x 100 mm)
Blind zone [mm]	100
Angle of aperture cylindrical [°]	16; (±1)
Max. deviation from the 90° angle sensor/object [°]	± 4



Full-metal ultrasonic sensor

UGA401000RRKG/AM/IO/US

Accuracy / deviations		
Temperature compensation	yes	
Hysteresis [%]	< 1	
Temperature drift	± 2 %; (of the final value of the measuring range)	
Repeatability	0,5 %	
Resolution [mm]	1	
Notes on the accuracy / deviation	The indicated values are reached after a warm-up time of min. 20 minutes	
Software / programming		
Parameter setting options	hysteresis / window; second switch point; Switch-on and switch-off delay; switch-on operations; Teach function; light-on/dark-on mode	
Interfaces		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9	
Profiles	Smart Sensor - SSP 4.1.1	Measuring and Switching Sensor, 1 channel
	Common - I&D	Identification and Diagnosis
	Extension	Sensor control
	Extension	Object detection, switches when value falls below the setpoint
	Function	Locator
	Function	ProductURI
SIO mode	yes	
Required master port class	A	
Min. process cycle time [ms]	3.2	
IO-Link process data (cyclical)	Function	bit length
	process value	16
	device status	4
	binary switching information	2
IO-Link functions (acyclical)	application specific tag; operating hours counter	
Supported DeviceIDs	Type of operation	DeviceID
	default	1812
Note	For further information please see the IODD PDF file at "Downloads"	
Operating conditions		
Ambient temperature [°C]	-20...70	
Storage temperature [°C]	-25...75	
Protection	IP 65; IP 67; IP 68; IP 69K	
Tests / approvals		
EMC	EN 61000-4-2 ESD	4 kV CD / 8 kV AD
	EN 61000-4-3 HF radiated	3 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	3 V
	EN 55011	class A
Vibration resistance	EN 60068-2-6 Fc	(10-55) Hz 1 mm amplitude, vibration duration 5 min., 30 min. per axis with resonance or 55 Hz



Full-metal ultrasonic sensor

UGA401000RRKG/AM/IO/US

Shock resistance	EN 60068-2-27 Ea	30 g 11 ms half-sine; 3 shocks each in every direction of the 3 coordinate axes
MTTF [years]		838
UL approval	Ta	-20...70 °C
	Enclosure type	Type 1
	voltage supply	Class 2
	File number UL	E174191

Mechanical data

Weight [g]	96.2
Housing	Threaded type
Dimensions [mm]	M18 x 1 / L = 98.5
Thread designation	M18 x 1
Material	housing: stainless steel (1.4404 / 316L); LED window: PA
Tightening torque [Nm]	50

Displays / operating elements

Display	Switching status	1 LED, yellow
---------	------------------	---------------

Accessories

Items supplied	lock nuts: 2 x M18, stainless steel
	damping plates: 2, EPDM

Remarks


Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: 4





Connection





Diagrams and graphs



- 1 Distance
- 2 Monitoring range
- 3 switch-on/switch-off graph
- 4 Target 100 x 100 mm
- 5 50 % of the target in the detection zone
- 6 Set point