
# E60028

## Flexible coupling for encoders

COUPLING 25-6-10-24-SV




1 M4 x 6 - ISO 4029 (4x)
2 Depth der Klemmnabe

| Mechanical data | | |
|---|---|---|
| Weight | [g] | 27 |
| Dimensions | [mm] | Ø 25 / L = 24 |
| Materials | | aluminium |
| Tightening torque | [Nm] | tightening torque screws: 120 Ncm |
| Outer diameter D | [mm] | 25 |
| Inner diameter 1 | [mm] | 6 |
| Inner diameter 2 | [mm] | 10 |
| Depth of the clamping hub | [mm] | 7 |
| Clamping screw | [mm] | M4 x 6 - ISO 4029 (4x) |
| Length | [mm] | 24 |
| Max. revolution, mechanical | [U/min] | 8000 |
| Max. axial shaft misalignment | [mm] | ± 0,5 |
| Max. radial shaft misalignment | [mm] | ± 0,3 |
| Max. angular displacement | [°] | ± 4,0 |

| Remarks | |
|---|---|
| Remarks | The data indicated apply to couplings with the above hub borings at an ambient temperature of 23 °C. |
| | The values of radial, angular and axial displacement are maximum values which must not reach their maximum simultaneously while in operation. |
| Pack quantity | 1 pcs. |